








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	30DEC2015	DL	CW
	B	ECR-21-122216	09DEC2021	WOR	CW



H24BP-T6-M
T2071244101-000
DOCKING FRAME FOR HMN INSERTS_FLOATING
6 MODULES




OTHER SPEC REFER TO
PN T2071244101-000

H24BP-T6-F
T2071244201-000
DOCKING FRAME FOR HMN INSERTS_FIXED
6 MODULES

注 释:

1. 技术参数:	
绝缘材料:	PC
阻燃等级:	UL94V-0
插拔次数:	500次



SPACING OF TWO PANELS AT CLOSE STATUS

T2071244201-000	H24BP-T6-F DOCKING FRAME FOR HMN INSERTS_FIXED HMN塑胶框架_固定端
T2071244101-000	H24BP-T6-M DOCKING FRAME FOR HMN INSERTS_FLOATING HMN塑胶框架_浮动端
PART NUMBER 料 号	PART DESCRIPTION 描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI	30DEC2015		 TE Connectivity	
		CHK CHRIS WANG	30DEC2015			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD XU XIANG	30DEC2015	NAME	
mm			PRODUCT SPEC		H24BP-T6-M/F	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC		DOCKING FRAME FOR HMN INSERTS	
MATERIAL	FINISH		WEIGHT		SIZE	CAGE CODE
-	-		-		A2	-
-	-					DRAWING NO
						G-T2071244X01000
CUSTOMER DRAWING				SCALE	SHEET	OF
				4.5	1	REV B