

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -






ALL RIGHTS RESERVED.

LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECR-19-005609	23MAY2019	BH	E.W
	F1	REVISED PER ECR-19-008330	24MAY2019	BH	E.W
	F2	REVISED PER ECR-19-013181	22AUG2019	BH	E.W
	F3	REVISED PER ECN-25-327375	16JUN2025	TDB	BKW



SCALE 1:2

- NOTES.
- 1.GENERAL TOLERANCE : ± 0.5
 - 2.APPLICABLE CONTACT P/N : 521843-1
 - 3.CAVITY MARK SHALL BE LOCATED APPROX. AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BH CHO	-	 TE Connectivity					
		CHK -	-						
DIMENSIONS: mm		APVD BW KANG	-	NAME					
		PRODUCT SPEC 108-61063		TERMINAL BLOCK FOR DRYER					
		APPLICATION SPEC -							
		SIZE	CAGE CODE					DRAWING NO	RESTRICTED TO
		A300779C-1743067							
MATERIAL PHENOLIC UL94 V-0		FINISH -	WEIGHT -						
		CUSTOMER DRAWING		SCALE 1:1	SHEET 1	OF 1	REV F3		

13.0 ^{+0.5} _{-0.1}	72.1 ± 0.25	$\varnothing 6.2 \pm 0.1$	BLACK	1743067-3
13.0 ^{+0.5} _{-0.1}	72.1 ± 0.25	$\varnothing 5.0 \pm 0.1$	BLACK	1743067-2
"Z"	"Y"	"X"	COLOR	P/N