




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B1	REVISED PER ECO-09-021480	08OCT2009	CR	DG
			B2	REVISED PER ECO-10-016367	02AUG2010	JY	SY
			B3	REVISED PER ECN-22-179890	17OCT2022	SK	DZ



1888861-2 AND 1888861-9
SHOWN WITHOUT PICK AND PLACE DEVICE



1888861-4 AND 1-1888861-0
SHOWN WITHOUT PICK AND PLACE DEVICE



1888861-8 AND 1-1888861-2
SHOWN WITHOUT PICK AND PLACE DEVICE

△ MATERIAL: LCP, BLACK.

△ MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.

△ FINISH: 0.76um MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03um MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81um MIN NICKEL PLATE PER QQ-N-290.


△ MATERIAL: NICKEL-SILVER PER ASTM B 122.

△ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.

6. REFER TO CUSTOMER DRAWING 1761987 FOR CONNECTOR DETAILS.

7. PACKAGED IN TAPE AND REEL PER EIA-481.

△ FINISH: 0.38um MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03um MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81um MIN NICKEL PLATE PER QQ-N-290.





1888861-6 AND 1-1888861-1
SHOWN WITHOUT PICK AND PLACE DEVICE

1-1888861-2 IS DISCONTINUED


△8	THRU HOLE	3.5	17.8	16	16	36	18.05	36	1-1888861-2
		2.8	17.8	16	16	36	18.05	36	1-1888861-1
	PRESS FIT	-	17.8	16	16	36	18.05	36	1-1888861-0
△3	THRU HOLE	2	17.8	16	16	36	18.05	36	1888861-9
		3.5	17.8	16	16	36	18.05	36	1888861-8
	PRESS FIT	-	17.8	16	16	36	18.05	36	1888861-6
△3	THRU HOLE	2	17.8	16	16	36	18.05	36	1888861-4
		2	17.8	16	16	36	18.05	36	1888861-2
FINISH	REMARKS	G	E	D	C	B	A	POSN	PART NUMBER

THIS DOCUMENT IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND THE BUYING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST EDITION.				DWN D. MCMASTER CHK D. GORENC APVD D. GORENC		21FEB07 21FEB07 21FEB07		Tyco Electronics Harrisburg, PA 17105-3608			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		EVERCLEAR Mini-SAS RIGHT ANGLE, INTERNAL RECEPTACLE ASSEMBLY, WITH UNKEYED SHELL					
mm		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-2234 APPLICATION SPEC		SIZE		CAGE CODE DRAWING NO		RESTRICTED TO	
MATERIAL SEE NOTES		SEE TABLE		WEIGHT -		A100779C=1888861		SCALE 8:1		SHEET 1 OF 3 REV B3	
CUSTOMER DRAWING											



LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



1888861-2



1888861-2
PICK AND PLACE DEVICE OMITTED FOR CLARITY



1888861-4
SAME AS 1888861-2 EXPECT AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN B. MCMASTER 21FEB07	 Tyco Electronics Harrisburg, PA 17105-3608		
DIMENSIONS: mm				CHK D. GORENC 21FEB07			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. GORENC 21FEB07	NAME EVERCLEAR Mini-SAS RIGHT ANGLE, INTERNAL RECEPTACLE ASSEMBLY, WITH UNKEYED SHELL		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-2234			
MATERIAL SEE NOTES		FINISH SEE TABLE		WEIGHT -	SIZE A100779	CAGE CODE C=1888861	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 6:1		SHEET 2 OF 3	REV B3

AMP 4805 REV 31MAR2000