




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F2	ECR-25-236041	25AUG2025	SY	DR

	
12-10 AWG STRANDED	12-10 AWG STRANDED



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 SEAM FACING UPWARD ON TAPE
- 3 SEAM FACING DOWNWARD ON TAPE
- 4 COPPER PER ASTM B-152, ANNEALED
- 5 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B545

OBSOLETE	50	LOOSE PIECE, BOX	8-31114-2
	2500	ON TAPE, REEL 3	31114-3
OBSOLETE	2500	ON TAPE, REEL 2	31114-2
	-	LOOSE PIECE	31114
	QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-8-93 CHK DA PATTERSON 2-8-93 APVD JL MECKLEY 2-8-93 PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	 TE Connectivity NAME TERMINAL, RING TONGUE, BUDGET -			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: N/A		FINISH - 4				
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED	MATERIAL - 4	FINISH - 5	SIZE A2	CAGE CODE 00779	DRAWING NO C-31114	RESTRICTED TO -
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			SCALE 10:1		SHEET 1 OF 1	REV F2		