



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	V4	REVISED PER ECR-25-255998	16SEP2025	SA	DSC

300 VOLT MAX		
AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED

300 VOLT MAX		
AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG STRANDED	12-10 AWG STRANDED	12-10 AWG STRANDED



- 1 WIRE INSULATION DIA 3.81 [.150] TO 5.59 [.220].
- 2 NOTE DELETED
-  3 TAPED PART LONG, CRIMP ONLY IN TAPETRONICS.

-	50	LOOSE PIECE, BOX	8-320570-2
-	1 KIT = 50 PIECES	LOOSE PIECE	6-320570-0
-	1500	ON TAPE, REEL	 2-320570-3
M7928/5-5 CLASS 1	50	LOOSE PIECE	320570
MILITARY PART NUMBER & CLASS PER MIL SPEC SAE AS7928	QTY	PACKAGE TYPE	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-28-93	 TE Connectivity
		CHK R. HERSEY 9-28-93	
		APVD T. MICHIELUTTI 9-28-93	
		PRODUCT SPEC	
DIMENSIONS: mm [INCHES] 		APPLICATION SPEC	NAME SPLICE, BUTT, PIDG, WIRE SIZE: 12-10 AWG
		WEIGHT -	
MATERIAL COPPER ASTM B-152		FINISH TIN PLATE	SIZE A3
			CAGE CODE 00779
			DRAWING NO C-320570
			RESTRICTED TO -
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1
			REV V4

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600V MAX 1000V MAX (FIXTURE OR SIGN)
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100]
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.