


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M5	REVISED PER ECR-25-255998	16SEP2025	SA	DSC

AMP
WIRE RANGE

24-20 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]



NOTE:
1. WIRE INSULATION DIA 1.02[.040] TO 2.54[.100]

-	1 KIT = 50 PIECES	LOOSE PIECE	6-323975-0
-	2500	ON TAPE	2-323975-3
M7928/5-2 CLASS 1	50	LOOSE PIECE	323975
MILITARY PART NUMBER & CLASS PER SAE AS7928	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105° C

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
0.16 - 0.65mm² [320-1,290]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
COPPER PER ASTM B-152
NYLON, COLOR:NATURAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.20[.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
TIN PLATE
PER MIL-T-10727

DWN
S.S. GOULDEN
9-28-93

CHK
R. HERSEY
9-28-93

APVD
S. BORTNER
9-28-93

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

TE Connectivity

NAME
SPLICE, BUTT, P.I.D.G.,
WIRE SIZE: 24-20 AWG
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-323975

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
M5