

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	PART 826947-1 REACTIVATION	08OCT2025	KS	SR




POS.	L $\begin{smallmatrix} +0.3 \\ -0.5 \end{smallmatrix}$	PART-NO.
1	-	826947 -1
2	5.08	<del>826947 -2</del> $\triangle$
3	7.62	<del>-3</del>
4	10.16	<del>-4</del>
5	12.70	<del>-5</del>
6	15.24	<del>-6</del>
7	17.78	<del>-7</del> $\triangle$
8	20.32	<del>-8</del>
9	22.86	<del>-9</del> $\triangle$
10	25.40	1- -0
11	27.94	1- <del>-1</del> $\triangle$
12	30.48	1- <del>-2</del> $\triangle$
13	33.02	1- <del>-3</del> $\triangle$
14	35.56	1- <del>-4</del> $\triangle$
15	38.10	1- <del>-5</del> $\triangle$
16	40.64	1- <del>-6</del>
17	43.18	1- <del>-7</del> $\triangle$
18	45.72	1- <del>-8</del> $\triangle$
19	48.26	1- <del>-9</del> $\triangle$
20	50.80	2- -0
21	53.34	2- <del>-1</del> $\triangle$
22	55.88	2- <del>-2</del> $\triangle$
23	58.42	2- <del>-3</del> $\triangle$
24	60.96	2- <del>-4</del> $\triangle$
25	63.50	2- <del>-5</del> $\triangle$
26	66.04	2- <del>-6</del> $\triangle$
27	68.58	2- <del>-7</del> $\triangle$
28	71.12	2- <del>-8</del> $\triangle$
29	73.66	2- <del>-9</del> $\triangle$
30	76.20	3- <del>-0</del> $\triangle$
31	78.74	3- <del>-1</del> $\triangle$
32	81.28	3- <del>-2</del> $\triangle$
33	83.82	3- <del>-3</del> $\triangle$
34	86.36	3- <del>-4</del> $\triangle$
35	88.90	3- <del>-5</del> $\triangle$
36	91.44	3- <del>-6</del>
37	93.98	3- <del>-7</del> $\triangle$
38	96.52	3- <del>-8</del> $\triangle$
39	99.06	3- <del>-9</del> $\triangle$
40	101.60	4- <del>-0</del> $\triangle$
41	104.14	4- <del>-1</del> $\triangle$
42	106.68	4- <del>-2</del> $\triangle$
43	109.22	4- <del>-3</del> $\triangle$
44	111.76	4- <del>-4</del> $\triangle$
45	114.30	4- <del>-5</del> $\triangle$
46	116.84	4- <del>-6</del> $\triangle$
47	119.38	4- <del>-7</del> $\triangle$
48	121.92	4- <del>-8</del> $\triangle$
49	124.46	4- <del>-9</del> $\triangle$
50	127.00	5- 826947 -0

$\triangle$  1 OBSOLETE

SEE DIAGRAM  
826629 SHEET 3

TE Connectivity. All Rights Reserved.

THERE IS NO ORIGINAL OF THIS DRAWING

DIMENSIONS: mm	DWN	-	MATERIAL	-	FINISH	-
	CHK	-	 TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-				
0 PLC $\pm$ -	PRODUCT SPEC	-	NAME			
1 PLC $\pm$ -	APPLICATION SPEC	-	AMPMODU II STIFTLAISTE 90DEG EINREIHIG			
2 PLC $\pm$ -	WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC $\pm$ -			A4	00779	$\text{C}$ -826947	-
4 PLC $\pm$ -			CUSTOMER DRAWING			SCALE
ANGLES $\pm$ -			SCALE			SHEET
 			SCALE			1 OF 1
			SCALE			REV P2