





COIL: @ 25°C  
 RESISTANCE 2000 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 14.2 VDC  
 MUST RELEASE 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.  
 RELEASE TIME 2.0 MS MAX.  
 CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/10/98 *CK* 9/10/98

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. QPL  
 CUST. NO. M39016/7-024M

TYPE "J1MA" RELAY

J1MAP-26XM