




REV. 0

DC0 143384

COIL: @ 25°C

RESISTANCE 390 OHMS $\pm$ 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 4.0 MS MAX

CONTACT STABILIZATION 2.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. HDS 1/14/02

1/14/02

CII Technologies
advanced control electronic solutions

CUST. QPL

CUST. NO. M39016/18-040P REV.

"JMGAD" RELAY

JMGACD-12PW