




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J2	ECR-25-239014	28APR2025	ABS	PS

- 1
- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2
- USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3
- THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5
- FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103649
- 6
- ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 8
- MAXIMUM ALLOWABLE BOW OF ASSEMBLY NOT TO EXCEED.055.
- 9
- CONTACTS: .000015 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 10
- CONTACTS: .000015 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 11
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

11	OBSOLETE	10	2	2.40	1.198	1-103648-1	12	6-103972-1
11	OBSOLETE	10	2	2.20	1.098	1-103648-0	1 1	6-103972-0
11	OBSOLETE	10	2	2.00	.998	103648-9	10	5-103972-9
11	OBSOLETE	10	2	1.80	.898	103648-8	9	5-103972-8
11	OBSOLETE	10	2	1.60	.798	103648-7	8	5-103972-7
11	OBSOLETE	10	2	1.40	.698	103648-6	7	5-103972-6
11	OBSOLETE	10	4	2.39	.598	103648-5	6	5-103972-5
	OBSOLETE	10	4	1.99	.498	103648-4	5	5-103972-4
		10	5	1.99	.398	103648-3	4	5-103972-3
	OBSOLETE	10	8	2.40	.298	103648-2	3	5-103972-2
	OBSOLETE	10	10	2.00	.198	103648-1	2	5-103972-1
11	OBSOLETE	9	2	2.40	1.198	1-103648-1	12	1-103972-1
11	OBSOLETE	9	2	2.20	1.098	1-103648-0	1 1	1-103972-0
11	OBSOLETE	9	2	2.00	.998	103648-9	10	103972-9
11	OBSOLETE	9	2	1.80	.898	103648-8	9	103972-8
11	OBSOLETE	9	2	1.60	.798	103648-7	8	103972-7
11	OBSOLETE	9	2	1.40	.698	103648-6	7	103972-6
11	OBSOLETE	9	4	2.39	.598	103648-5	6	103972-5
	OBSOLETE	9	4	1.99	.498	103648-4	5	103972-4
SUPERSEDED BY 5-103972-3		9	5	1.99	.398	103648-3	4	103972-3
		9	8	2.40	.298	103648-2	3	103972-2
	OBSOLETE	9	10	2.00	.198	103648-1	2	103972-1

PLATING	6	B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP
---------	---	---	---	---------------------	------------	-------------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. MAYER 05 NOV 1986	TE Connectivity		
DIMENSIONS: INCHES		CHK P.C.DEJONG 12-11-86			
		APVD — 13-11-86	NAME		
		PRODUCT SPEC 108-25034			
HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR:BLACK CONTACTS: PHOS BRONZE		APPLICATION SPEC 114-25026		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
FINISH SEE TABLE		CUSTOMER DRAWING		DRAWING NO C=103972	
		SCALE 4:1		SHEET 1 OF 1	
				REV J2	