



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECO-09-020932	03SEP09	KK	AEG
	B2	PART OBSOLESCENCE	27APR2026	LS	SRK


D




C



B



A



RECOMMENDED BOARD LAYOUT

SCALE - 5:1

SECTION W-W

DETAIL P

BASIC DIMENSIONS FOR
ODD NUMBER OF SPACES

- 0.00076[.000030] GOLD AT POINT OF MEASUREMENT, 0.00051[.000020] MIN AT THE END POINTS OF AREA G, (LOCALIZED PLATE AREA), 0.0038[.000150] TIN-LEAD ON LOCALIZED TIN-LEAD PLATED AREA, ALL OVER 0.0013[.000050] NICKEL
- DIMENSION APPLIES AT BASE OF SHROUD.
- THE NOTED DIMENSIONS APPLY AT THE MATING FACE OF THE HOUSING.
- POINT OF MEASUREMENT.
- DIMENSIONS NOTED APPLY FROM THE BASIC DIMENSION LINE (NOT THE CIRCUIT CAVITY CENTER LINE) TO THE SURFACE INDICATED.
- IF PLANNING TO USE MORE THAN ONE MATING PAIR OF CONNECTORS TO INTERCONNECT 2 BOARDS, PLEASE REFER TO PARA. 3.3 IN THE APPLICATION SPEC, #114-7010
- KAPTON VACUUM PICK UP BUTTON (SHOWN IN PHANTOM TO SHOW CONNECTOR DETAIL). 13.0±.25[.512±.010] DIAMETER LOCATED Φ Ø1.0 [.039] Z Y
- PACKAGED IN EIA 481 TAPE AND REEL. SEE TABLE FOR TAPE WIDTHS.
- 0.00076 (.000030) GOLD AT POINT OF MEASUREMENT, 0.00051 (.000020) MIN AT THE END POINTS OF AREA G, (LOCALIZED PLATE AREA), 0.00381 (.000150) TIN ON LOCALIZED TIN PLATED AREA, ALL OVER 0.00127 (.000050) NICKEL.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

		32.0	9.45 [.372]	6.91 [.272]	4	10	Δ 5-147119-2
Δ 10	OBSOLETE	44.0	15.79 [.622]	13.25 [.522]	9	20	Δ 5-147119-4
	OBSOLETE	32.0	9.45 [.372]	6.91 [.272]	4	10	-147119-2-
Δ 10	OBSOLETE	44.0	15.79 [.622]	13.25 [.522]	9	20	-147119-4-
		TAPE WIDTH	C	B	A	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HAYMAKER 18NOV98	TE Connectivity				
DIMENSIONS: mm (INCHES)		CHK D. SIMPSON 18NOV98	NAME				
		APVD D. SIMPSON 18NOV98	PRODUCT SPEC				
			APPLICATION SPEC				
			SIZE				
			CAGE CODE				
			DRAWING NO				
			RESTRICTED TO				
			WEIGHT				
			A1 00779 C=147119				
			CUSTOMER DRAWING				
			SCALE 8:1				
			SHEET 1 OF 1				
			REV B2				