






- △ DIMENSIONS PER CUSTOMER BOARD LAYOUT
- △ FINISH: 1.27μM MIN GOLD IN CONTACT AREA, 1.27μM MIN TIN-LEAD ON PCB TAIL, OVER 1.27μM MIN NICKEL OVER ALL.
- △ FINISH: 1.27μM MIN GOLD IN CONTACT AREA, 1.27μM MIN TIN ON PCB TAIL, OVER 1.27μM MIN NICKEL OVER ALL.
4. HOUSING: LCP, UL94V-0, BLACK
CONTACT: PHOSPHOR BRONZE
- △ OBSOLETE PART NUMBER.



OBSOLETE

△	SUPERCEDED BY 1-1410271-9
△	SUPERCEDED BY 1-1410271-8
△	SUPERCEDED BY 1-1410271-7
△	SUPERCEDED BY 1-1410271-6
△	SUPERCEDED BY 1-1410271-5
△	SUPERCEDED BY 1-1410271-4
△	SUPERCEDED BY 1-1410271-3

△	13.75	13.75	12.25	12.25	2-1410271-2
△	13.75	13.75	12.25	12.25	2-1410271-1
	12.25	10.75	10.75	12.25	2-1410271-0
	10.75	12.25	13.75	10.75	1-1410271-9
	10.75	10.75	10.75	10.75	1-1410271-8
	10.75	12.25	12.25	10.75	1-1410271-7
	12.25	12.25	12.25	12.25	1-1410271-6
	10.75	12.25	13.75	12.25	1-1410271-5
	10.75	13.75	13.75	10.75	1-1410271-4
	10.75	13.75	13.75	12.25	1-1410271-3
	12.25	13.75	13.75	12.25	1-1410271-2
△	13.75	13.75	13.75	13.75	1-1410271-1
	12.25	10.75	10.75	12.25	1-1410271-0
	10.75	12.25	13.75	10.75	△ 1410271-9
	10.75	10.75	10.75	10.75	1410271-8
	10.75	12.25	12.25	10.75	1410271-7
	12.25	12.25	12.25	12.25	1410271-6
	10.75	12.25	13.75	12.25	1410271-5
	10.75	13.75	13.75	10.75	△ 1410271-4
	10.75	13.75	13.75	12.25	1410271-3
	12.25	13.75	13.75	12.25	1410271-2
PLATING	13.75	13.75	13.75	13.75	1410271-1
	CAVITY #4 "L"	CAVITY #3 "L"	CAVITY #2 "L"	CAVITY #1 "L"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±0.3
1 PLC	±0.25
2 PLC	±0.25
3 PLC	±0.25
4 PLC	±0.25
ANGLES	±1°
FINISH	

MATERIAL

FINISH

DWN: L.A.MAYER 10SEP2000

CHK: S.WELLER 10SEP2000

APVD: S.FLICKINGER 10SEP2000

PRODUCT SPEC: 108-2062

APPLICATION SPEC: 114-13062

WEIGHT: -

CUSTOMER DRAWING

NAME: ASSEMBLY, POWER, RIGHT ANGLE HEADER, 4 CAVITY, 20.3mm, MULTIGIG

SIZE: 00779

CAGE CODE: 1410271

DRAWING NO: 1410271

RESTRICTED TO: -

TE Connectivity

SCALE: 6:1

SHEET: 1 OF 1

REV: A7