





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	ECO-19-006934	13MAY2019	AP	WS
	C	REVISED PER ECN-20-100924	15DEC2020	WLS	VS
	C1	REVISED PER ECN-23-242776	13DEC2023	WLS	VS
	C2	REVISED PER ECN-25-316179	08MAY2025	WLS	JP



- ① MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP., NYLON, COLOR BLACK.
CONTACTS - BRASS
- ② RECOMMENDED PC BOARD THICKNESS OF 1.57.
- ③ PLATING: CONTACTS - 2.54μm MINIMUM MATTE TIN OVER 1.27μm MINIMUM NICKEL.
- 4 COUNTERPART RECOMENDED IS PN 1445022 (DASH ACCORDING TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTIONAND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	-32.20	37.00	28.70	33.00	40.14	12	3-1445055-2
OBSOLETE	-29.20	34.00	25.70	30.00	37.14	11	3-1445055-1
OBSOLETE	-26.20	31.00	22.70	27.00	34.14	10	3-1445055-0
	23.20	28.00	19.70	24.00	31.14	9	2-1445055-9
	20.20	25.00	16.70	21.00	28.14	8	2-1445055-8
	17.20	22.00	13.70	18.00	25.14	7	2-1445055-7
	14.20	19.00	10.70	15.00	22.14	6	2-1445055-6
	11.20	16.00	7.70	12.00	19.14	5	2-1445055-5
	8.00	13.00	4.70	9.00	16.14	4	2-1445055-4
	3.30	10.00	-	6.00	13.14	3	2-1445055-3
	3.30	7.00	-	3.00	10.14	2	2-1445055-2
	DIM X	DIM Y	DIM V	DIM Z	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.ROOT 06OCT2000 CHK K.WHITAKER 13-MAR-2001 APVD K.WHITAKER 13-MAR-2001		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±1° MATERIAL FINISH		NAME RIGHT ANGLE THRU HOLEHEADER ASSY, TIN CONTACTS W/PLASTIC HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK TM			
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000 WEIGHT -		SIZE A2		CAGE CODE 00779	
				DRAWING NO C=1445055		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 2	
						REV C2	

