

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C6	REVISED PER ECN-23-242776	13DEC2023	WLS	VS
	D	REVISED PER ECN-25-316179	12MAY2025	WLS	JP

D

D

C




C

B


B

A

A



- 1 MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING: CONTACTS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.
- 6 ALL SOLDER TAILS AND STANDOFFS.



OBSOLETE	37.00	33.00	37.43	40.00	12	3-1445056-2
OBSOLETE	34.00	30.00	34.43	37.00	11	3-1445056-1
OBSOLETE	31.00	27.00	31.43	34.00	10	3-1445056-0
OBSOLETE	28.00	24.00	28.43	31.00	9	2-1445056-9
OBSOLETE	25.00	21.00	25.43	28.00	8	2-1445056-8
OBSOLETE	22.00	18.00	22.43	25.00	7	2-1445056-7
OBSOLETE	19.00	15.00	19.43	22.00	6	2-1445056-6
OBSOLETE	16.00	12.00	16.43	19.00	5	2-1445056-5
	13.00	9.00	13.43	16.00	4	2-1445056-4
	10.00	6.00	10.43	13.00	3	2-1445056-3
	7.00	3.00	7.43	10.00	2	2-1445056-2
	DIM X	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.ROOT 03OCT2000	TE Connectivity			
DIMENSIONS: mm		CHK K.WHITAKER 13-MAR-2001				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.WHITAKER 13-MAR-2001	NAME RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/THRU HOLE HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™			
0 PLC ± 1 PLC ± 2 PLC ±0.20 3 PLC ± 4 PLC ±		PRODUCT SPEC 108-1836				
ANGLES ±1°		APPLICATION SPEC 114-13000	SIZE A2	CAGE CODE 00779	DRAWING NO C-1445056	RESTRICTED TO -
MATERIAL 1		WEIGHT -	CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2
3					REV D	

