




REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	G	REVISED	20AUG2011	H. U	N. Y	
	H	REVISED PER ECR-14-000206	26DEC2013	PV	RB	
	H1	REVISED ECR-22-131396	03MAR2022	KF	AO	
	H2	REVISED PER ECR-24-230839	07JAN2025	HY	AO	




1871414-2
SCALE 2:1



—|87|4|4—3— 
SCALE 2:1



187 | 4 | 4 | 4 — 
SCALE 2:1




SCALE 2:1


- | | |
|---|--|
| 1 | MATERIAL: 15% GLASS FILLED THERMOPLASTIC
COLOR: BLACK |
| 2 | MATERIAL: 15% GLASS FILLED THERMOPLASTIC
COLOR: (SEE TABLE) |
| 3 | MATERIAL: SILICONE
COLOR: RUST |

4 WIRE INSULATION RANGE: $\varnothing 1.3 \sim \varnothing 2.54$



- ## 5 OBSOLETE PARTS



SECTION A - A



1871414-1 SHOWN



5 OBSOLETE	GREEN	1871414-4
	YELLOW	1871414-3
	GRAY	1871414-2
	RED	1871414-1
	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN Y. KATO 28DEC2005		 TE Connectivity								
			CHN J. AKASAKA 28DEC2005										
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±.		APVD D. MITSUGI 28DEC2005		NAME CAP ASSY, 4 POS. BRACKET REVERSE TYPE SMALL WIRE SIZE AMP SEAL 16							
				PRODUCT SPEC 108-2184									
				APPLICATION SPEC 114-13065									
				MATERIAL				FINISH		WEIGHT			
-		-		-		A200779		DRAWING NO C-1871414		RESTRICTED TO -			
-		-		-		CUSTOMER DRAWING		SCALE 3:1		SHEET OF		REV H2	
-		-		-									