



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECN-25-333917	21JUL2025	SP	JG



- 1 WIRE INSULATION: .490—.574 DIA.
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 STAMP "AMP 2/0 AL N" SIZE AND LOCATION APPROX AS SHOWN.
4. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-2281 FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 2 FOR WIRE STRIPPING DETAILS.



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL QQ-N-290 .000300 AVG THK	1958080-1
BODY: COPPER ASTM-B187 ANNEALED NICKEL PL .000300 MIN THK PER QQ-N-290	
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR. RUTH 31JAN07	TE Connectivity		
DIMENSIONS: INCHES		CHK JOHN KNOLL 31JAN07			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JOHN KNOLL 31JAN07	NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM, WIRE SIZE: 2/0 ALUMINUM		
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT 98 GRAMS	SIZE A2	CAGE CODE 00779	DRAWING NO C=1958080
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV G