



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	WIRE RANGE IS UPDATED	26OCT2018	SV	PKS

D



IDENTIFICATION NUMBER 9
FOR MAGNET WIRE RANGE



3.43
[.135] MAX
FREE STATE

32°±5°


0.38
[.015]

7.87
[.310]

0.406 ± 0.025
[.016 ± .001]

3.05 [.120]
2.95 [.116]

- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 5.59±0.08[.220±.003] CENTERS.
- 2 SLOT ACCEPTS A SINGLE OR DOUBLE WIRE ONLY
COPPER WIRE RANGE 0.36–0.51mm [#27–#24] AWG
ALUMINUM WIRE RANGE 0.45–0.51mm [#25–#24] AWG
- 3 POKE-IN ACCEPTS A 0.50–0.90 mm² [#20–#18 AWG]
SOLID OR FUSED STRANDED LEAD WIRE.
- 4 PART WILL ACCEPT EITHER POKE-IN TAB OR FUSED LEAD WIRE.



C

B


A

D

C

B

A

PAPER		CARDBOARD REEL		TIN PLATED		BRASS		2825380–1			
SPLICE		REELING MATERIAL		FINISH		MATERIAL		PART NO			
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN 09NOV2016 BASVESH WARAD		 TE Connectivity					
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 09NOV2016 SUBRAMANIAN, VIJAI						NAME	
				APVD 09NOV2016 SUBRAMANIAN, VIJAI							
		0 PLC ± – 1 PLC ± – 2 PLC ± 0.25 [0.10] 3 PLC ± – 4 PLC ± – ANGLES ± –		PRODUCT SPEC		TERMINAL, POKE-IN, 300 SERIES MAG-MATE –					
				108–2012							
				APPLICATION SPEC		114–2046		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2 00779 C=2825380					
SEE TABLE		SEE TABLE		CUSTOMER DRAWING		SCALE		SHEET		REV	
						10:1		1 of 1		A2	