





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	RELEASED	13APR2026	F.Z	L.L



SECT "A"-"A"




SECT "B"-"B"



WIRE RANGE ID MARK

CONTACT ID MARK




FORMING ID No

BLANKING ID MARK

REF

23.9 —



TRADE MARK

PLATING ID NO


NOTES

1. FINISH(CONTACT AREA):0.38 μ mMIN PdNi & Au FLASH OVER Ni PLATING
2. FINISH(CONTACT AREA):0.76 μ mMIN PdNi & Au FLASH OVER Ni PLATING
3. FINISH(CONTACT AREA):2.54 μ mMIN SILVER PLATING OVER Ni PLATING

WIRE SIZE: AWG 12#~AWG 10#

INSULATION DIA: 4~5.2mm

6		179956-6	316041-6
8		179956-3	316041-3
7		179956-2	316041-2
PL ID CODE	(FINISH)	MATERIAL	L/P
			(P/N)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Fisher ZHU 13APR2026		 TE Connectivity	
		CHK Liam LING 13APR2026			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME — DYNAMIC D-5000 SERIES REC CONTACT "M" SIZE L/P	
		0 PLC ± — ±0.3 1 PLC ± — ±0.35 2 PLC ± — ±0.4 3 PLC ± — ±3' 4 PLC ± — ANGLES ± —			
		PRODUCT SPEC 108-5453			
		APPLICATION SPEC 114-5206			
MATERIAL COPPER ALLOY		FINISH SEE TABLE		WEIGHT —	
				SIZE A3	
				CAGE CODE 00779	
				DRAWING NO C-316041	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1	
				SHEET 1 OF 1	
				REV F	