


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D5	REVISED PER ECR-25-255998	15SEP2025	SA	DSC



- 1 FOR 1.02[.040] TO 2.54[.100] WIRE INSULATION DIA
- 2 TONGUE MATERIAL THK 0.58±0.05[.023±.002]

3 APPLIES FROM EDGE OF METAL BARREL TO CENTERLINE OF STUD HOLE.

1 KIT = 250 PIECES	WIRE TERMINAL	BODY&SLEEVE: COPPER ASTM-B152 TIN PL ASTM-B545 INSULATION: NATURAL NYLON ASTM-D4066 TYPE I	6-323989-0
1	323989 ON TAPE		1-323989-0
1	WIRE TERMINAL		323989
QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 19MAR10	TE Connectivity		
		CHK JEFF RUTH 19MAR10			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD TOM MICHIELUTTI 19MAR10	NAME TERMINAL, NYLON - PIDG - RING TONGUE WIRE SIZE: 24-20 AWG		
	0 PLC ± -	PRODUCT SPEC			
	1 PLC ± -	APPLICATION SPEC			
MATERIAL SEE TABLE	2 PLC ± -	WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-323989
	3 PLC ± 0.20 [.008]				
	4 PLC ± -				
	ANGLES ± 0° 30'				
	FINISH				
	SEE TABLE				
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV D5