




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M1	REVISED PER ECN-25-360726	20JAN2026	CM	RE




- 1 CONTINUOUS STRIP ON REELS
- 2 TIN PLATING.
- 3 P/N 42751-5 REELED WITH INTERLEAF PAPER.



obsolete	#2 HARD BRASS	-	.120-.180 DIA	16-14 AWG	3 42751-5
	1/4 HARD PHOS BRONZE	-			42751-3
	#2 HARD BRASS	2			42751-2
	#2 HARD BRASS	-			42751-1
MATERIAL		FINISH	INSULATION RANGE	WIRE SIZE	PART NO.

F or O	.210	.220	F	.155	.087	14
					.081	16
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 4/16/90	 TE Connectivity			
DIMENSIONS: INCHES		CHK JR RUTH 4/16/90				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G YETTER 4/16/90				
		PRODUCT SPEC	RING			
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		0.000000	A3	00779	C-42751	-
FINISH		CUSTOMER DRAWING		SCALE	SHEET	REV
SEE TABLE				4:1	1 OF 1	M1