

D


C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K4	REVISED PER ECR-25-255998	12SEP2025	SA	DSC

 AMP WIRE RANGE	 FILE E13288	 LR7189 Certified
8 AWG STRANDED	8 AWG STRANDED	8 AWG STRANDED



- 1

STAMP AMP 8* LOCATE APPROX AS SHOWN
- 2

BODY MATERIAL THK 0.991±0.051[.039±.002]
- 3

WIRE INSULATION Ø8.382[Ø.330] MAX
- 4

NOTE DELETED
- 5

NOTE DELETED


D

C

B

A

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX. RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600V MAX	
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 6.64-10.5mm²[13,100-20,800] STRANDED	
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR. RUTH 19DEC02	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R. HERSEY 19DEC02				
		APVD T. MICHIELUTTI 19DEC02	NAME TERMINAL, RING TONGUE, PLASTI-GRIP, 8 AWG			
		PRODUCT SPEC UL 486 A-B				
MATERIAL BODY: COPPER ASTM-B152 INSULATION: PVC		FINISH BODY: TIN PLATE ASTM-B545 INSULATION: COLOR: RED	APPLICATION SPEC 114-2161	SIZE A2	CAGE CODE 00779	DRAWING NO C=52262
WEIGHT CUSTOMER DRAWING			RESTRICTED TO -			
			SCALE 4:1	SHEET 1 OF 1	REV K4	

52262