

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M1	ECR-26-274353	23MAR2026	ABS	PS

- △1 CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF .125 TOLERANCES NON-CUMULATIVE.
- △2 USE EXTRACTION TOOL 91052-2 TO REMOVE RECEPTACLE CONTACTS.
- △3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

D

D

C




C

B

B

A

A



SECT X-X

	OBSOLETE	1.610	.750	.750	13	1-86402-7
	OBSOLETE	1.360	.625	.625	11	1-86402-6
	OBSOLETE	3.485	1.625	1.750	28	1-86402-5
SUPERSEDED BY	1-86401-4	.735	.250	.375	6	1-86402-4
	OBSOLETE	2.985	1.375	1.500	24	1-86402-3
	OBSOLETE	2.235	1.000	1.125	18	1-86402-2
	OBSOLETE	2.110	.875	1.125	17	1-86402-1
	OBSOLETE	1.985	.875	1.000	16	1-86402-0
△3	OBSOLETE	.360	.125	.125	3	86402-9
SUPERSEDED BY	86401-8	1.235	.500	.625	10	86402-8
△3	OBSOLETE	1.735	.750	.875	14	86402-7
△3	OBSOLETE	.610	.250	.250	5	86402-6
	OBSOLETE	.235	.125	-	2	86402-5
		1.485	.625	.750	12	86402-4
	OBSOLETE	.985	.375	.500	8	86402-3
	OBSOLETE	.485	.125	.250	4	86402-2
		2.485	1.125	1.250	20	86402-1
		C	B	A	NO OF POS	PART NUMBER (MARKED)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BOB BOLES BG 14SEP89	TE Connectivity			
DIMENSIONS: INCHES		CHK J. GESFORD 23OCT89				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 0°30'		CONNECTOR, CRIMP SNAP-IN, MOD IV, SINGLE ROW, .125 CENTERS.			
	FINISH		SIZE A2			
MATERIAL GLASS FILLED NYLON COLOR-BLACK		WEIGHT	CAGE CODE	DRAWING NO C=86402	RESTRICTED TO	
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV M1	