




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	04JAN2016	RL	CW
	B	ECR-21-105887	26JUL2021	BS	CW
	C	ECR-22-150866	21SEP2022	DL	CW
	D	ECR-25-237606	30MAY2025	ABS	RB

- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: -40-+125°C
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X20XX000)




- 注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: -40-+125°C
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T20200X20XX000)




GROUND CONTACT SCREW:
M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2Nm
接地压线螺丝: M4螺丝推荐拧紧力矩1.2Nm



FIXING SCREW: 4xM3
RECOMMENDED TIGHTENING
TORQUE 0.5Nm
固定螺丝: 4xM3螺丝推荐拧紧力矩0.5Nm



PANEL CUT OUT FOR INSERTS FOR USING
WITHOUT HOODS/HOUSINGS
不带壳体时面板开孔尺寸

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROY LIU 04JAN2016		TE Connectivity													
		CHK KYLE ZENG 04JAN2016															
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHRIS WANG 04JAN2016		NAME HDD-016-M											
		0 PLC ±-		PRODUCT SPEC		SIZE A3		CAGE CODE 00779		DRAWING NO C-T2030162101000		RESTRICTED TO -					
		1 PLC ±-		108-137043													
		2 PLC ±-		APPLICATION SPEC													
3 PLC ±-		4 PLC ±-		114-137043													
4 PLC ±-		ANGLES ±-		WEIGHT -													
MATERIAL -		FINISH -		CUSTOMER DRAWING								SCALE 1:1		SHEET 1 OF 1		REV D	
-		-															