



intercontec
products

Kontaktstift ø1,0mm

Einsatzbereich: - 723 htec
- 740 htec
- 623 10-polig
- 923 8- und 9-polig

TE Teile Nr.: 61-0221-011-P00
IC Ref. Nr.: 61.221.11

Elektrische Werte

Bemessungsstrom max. 14 A*
Durchgangswiderstand < 5 mOhm

Werkstoff

Kontakt Messing, vergoldet

Anschluss

Anschlussart/-bereich Crimp/ 0,50 - 1,5 mm²
max. Litzenaußendurchmesser ø2,5 mm
Abisolierlänge 5 mm

Mechanische Werte


Steckzyklen 500

Werkzeuge (nicht im Lieferumfang enthalten)

digitale Crimpzange TE Teile Nr.: C0-0236-000-000
IC Ref. Nr.: C0.236.00

(analoge Crimpzange TE Teile Nr.: C0-0201-000-000
IC Ref. Nr.: C0.201.00

Positioniereinsatz für 1mm Kontakte TE Teile Nr.: C0-0252-000-000
IC Ref. Nr.: C0.252.00)





intercontec
products

Contact Pin $\varnothing 1.0\text{mm}$

for: - 723 htec
- 740 htec
- 623 10-pin
- 923 8- and 9-pin

TE part number: 61-0221-011-P00
IC reference number: 61.221.11

Electrical Data

rated current max. 14 A*
contact resistance < 5 mOhm

Material

contact brass, gold plated

Termination

cross-section crimp/ 0.50 - 1.50 mm²
max. outer wire diameter $\varnothing 2.5\text{ mm}$
stripping length 5 mm

Mechanical Data

mating cycles 500

Tools (not part of product contents)

digital crimping tool TE part no.: C0-0236-000-000
IC ref. no.: C0.236.00

(analog crimping tool TE part no.: C0-0201-000-000
IC ref. no.: C0.201.00

positioning insert for 1mm contacts TE part no.: C0-0252-000-000
IC ref. no.: C0.252.00)

