






P	LTR	DESCRIPTION	DATE	DWN	APVD
	B4	ADDED VIEW IN ZONE C2,D2	21FEB2025	PK	VNB



SECTION M-M



SECTION Z-Z



1. WIRE RANGE: 8 - 10 AWG
2. INSULATION RANGE: .176 - .272
3. FINISH: NICKEL PLATE ALL OVER 0.000050 MIN THICK
4. FINISH: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA
5. FINISH: TIN IN AREA INDICATED 0.000050 - 0.000100 THK.
6. MATERIAL: HIGH CONDUCTIVITY COPPER ALLOY
7. FINISH: TIN-LEAD IN AREA INDICATED 0.000050 - 0.000100 THK.

.315	1.200	  	STD	2-1600960-4
.315	1.250	  	MFBL	2-1600960-1
.228	1.200	  	STD	1-1600960-8
.228	1.250	  	MFBL	1-1600960-7
.228	1.200	  	STD	1-1600960-0
.228	1.250	  	MFBL	1600960-9
DIM A	DIM F REF	FINISH	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 19 JAN 2005 R. GRZYBOWSKI		TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: D'AMATO		NAME D'AMATO	
		PRODUCT SPEC 108-2157 APPLICATION SPEC 114-13112		VERTICAL BULKHEAD CABLE RECEPTACLE POWER CONTACT MULTI-BEAM XL	
MATERIAL		WEIGHT		SIZE	CAGE CODE
SEE NOTES material_2		-		A2	00779
FINISH		CUSTOMER DRAWING		DRAWING NO	RESTRICTED TO
SEE NOTES finish_spec_2				1600960	-
SCALE				SHEET	REV
6:1				OF	B4