






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	DI	REVISED PER ECO-19-013973	16SEP2019	RS	WLS
	E	REVISED PER ECO-20-013993	01OCT2020	WLS	VS
	F	REVISED PER ECN-25-313010	03APR2025	WLS	JP

- 1 WIRE RANGE: 26-30 AWG.
- 2 INSULATION RANGE: 0.89-1.52 mm.
- 3 2.54 μ m MIN. THK. BRIGHT TIN ENTIRE STOCK OVER
1.27 μ m MIN. THK. NICKEL ENTIRE STOCK.
- 4 2.54 μ m MIN. THK. BRIGHT TIN IN LOCALIZED TIN PLATE AREA,
OVER 1.27 μ m MIN. THK. NICKEL ON ENTIRE STOCK.
- 0.38 μ m MIN. THK. GOLD,
OR
0.0762 μ m MIN. THK. GOLD FLASH OVER 0.31 μ m MIN. THK. PALLADIUM NICKEL
IN THE GOLD PLATE AREA PER TE CONNECTIVITY'S DISCRETION,
- 5 2.54 μ m MIN. THK. BRIGHT TIN IN LOCALIZED TIN PLATE AREA,
OVER 1.27 μ m MIN. THK. NICKEL ON ENTIRE STOCK.
- 0.76 μ m MIN THK. GOLD,
OR
0.0762 μ m MIN. THK. GOLD FLASH OVER 0.69 μ m MIN. THK. PALLADIUM NICKEL
IN THE GOLD PLATE AREA PER TE CONNECTIVITY'S DISCRETION,
- 6 TIN PLATING THICKNESS INSIDE WIRE AND INSULATION BARRELS
TO BE 1.27 μ m MIN.




SECTION Y - Y



SECTION Z - Z

5	1-794609-2
4	1-794609-1
3	1-794609-0
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W J RUDY 29AUG2000	 TE Connectivity			
DIMENSIONS: mm		CHK W DAVIS 29AUG2000				
		APVD W DAVIS 29AUG2000	NAME PLUG CONTACT, CRIMP SNAP, 26-30 AWG, MICRO MATE-N-LOK(TM)			
		PRODUCT SPEC 108-1836	-			
MATERIAL 0.20 THK BRASS		APPLICATION SPEC 114-13000	SIZE A200779		DRAWING NO C-794609	RESTRICTED TO
		WEIGHT -				REV F
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1	OF 1	