




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	PART STATUS CHANGE TO DISCONTINUNACE	01JUL2026	NS	PS

MATERIALS:
HOUSING: NYON, UL94V-0, BLACK.
TERMINALS: TIN PLATED, COPPER ALLOY.
SCREW: M3.5, NICKEL PLATED STEEL.


ELECTRICAL PROPERTIES:
RATING: 15A, 300V.
WIRE RANGE: 14-22 AWG.
TIGHTENING TORQUE: 12 IN-LB.

ENVIRONMENTAL PROPERTIES:
MAX OPERATING TEMP.: 120°C



RECOMMENDED PCB LAYOUT

OBSOLETE	3.000	2.625	8	1546833-8
OBSOLETE	2.625	2.250	7	1546833-7
	2.250	1.875	6	1546833-6
OBSOLETE	1.875	1.500	5	1546833-5
	1.500	1.125	4	1546833-4
	1.125	.750	3	1546833-3
	.750	.375	2	1546833-2
	DIM L	DIM A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL	08OCT03	 TE Connectivity	
		CHK S YODER	10/8/03		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S YODER	10/8/03	NAME - .375 MODULAR TRIBARRIER W/ COVER, ASSEMBLY	
		PRODUCT SPEC -			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APPLICATION SPEC -		SIZE	CAGE CODE
		WEIGHT -		A3	00779
MATERIAL -	FINISH -	DRAWING NO C-1546833		RESTRICTED TO -	
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV D2