







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-16-005516	25APR2016	DLD	CJS
	C1	REVISED PER ECN-26-377155	27APR2026	SMR	CS



- 1 MATERIAL: COPPER ALLOY C511
- 2 FINISH: PRE-PLATED WITH 1.00µm MIN BRIGHT TIN
- 3 MATERIAL ID FEATURE IN "DOWN" POSITION.
4. THE INTENDED TEMPERATURE RANGE FOR THIS TERMINAL IS -40°C TO +100°C.
5. TERMINAL HAS NYE LUBRICANTS NYETACT 568J-50-UV PERFORMANCE LUBE/GREASE APPLIED. THIS IS A WHITISH COLORED LUBE. AMOUNT AND VISIBILITY MAY VARY.
- 6 MATERIAL: COPPER ALLOY C425

PART NUMBERS - SEE SHEET 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN F. KINSEY	17DEC2007	 TE Connectivity	
		CHK F. KINSEY	17DEC2007		
		APVD J. MYER	17DEC2007		
		PRODUCT SPEC			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± ⁺		CONTACT,	
		1 PLC ± ⁺		0.64mm, FEMALE, GENERATION Y,	
		2 PLC ±0.15		UNSEALED APPLICATIONS	
		3 PLC ± ⁺		SIZE	
		4 PLC ± ⁺		108-2296	
		ANGLES		APPLICATION SPEC	
		FINISH		114-13183	
MATERIAL	-	WEIGHT		A100779C=1924955	
SEE TABLE	SEE TABLE	CUSTOMER DRAWING		SCALE 15:1	SHEET 1 OF 2 REV C


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL B	1.40	2.40	0.80	1.85	 		2 x 0.13mm ²	2-1924955-8
								0.35mm ²	
0.85 - 1.05	DETAIL B	0.85	1.82	0.65	1.50	 		26 [0.13mm ²]	2-1924955-7
0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL A	1.40	2.40	0.80	1.85	 		2 x 0.13mm ²	2-1924955-6
								0.35mm ²	
0.85 - 1.05	DETAIL A	0.85	1.82	0.65	1.50	 		26 [0.13mm ²]	2-1924955-5
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96	 		18 [0.75mm ²]	2-1924955-4
1.5 - 1.85	DETAIL B	1.78	2.94	0.80	1.82	 		20-22 [0.50-0.35mm ²]	2-1924955-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96	 		18 [0.75mm ²]	2-1924955-2
1.5 - 1.85	DETAIL A	1.78	2.94	0.80	1.82	 		20-22 [0.50-0.35mm ²]	2-1924955-1
0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL B	1.40	2.40	0.80	1.85	 		2 x 0.13mm ²	1924955-8
								0.35mm ²	
0.85 - 1.05	DETAIL B	0.85	1.82	0.65	1.50	 		26 [0.13mm ²]	1924955-7
0.13 = 0.85 - 1.05; 0.35 = 1.10 - 1.40	DETAIL A	1.40	2.40	0.80	1.85	 		2 x 0.13mm ²	1924955-6
								0.35mm ²	
0.85 - 1.05	DETAIL A	0.85	1.82	0.65	1.50	 		26 [0.13mm ²]	1924955-5
2.06 MAX	DETAIL B	1.78	2.94	1.00	1.96	 		18 [0.75mm ²]	1924955-4
1.5 - 1.85	DETAIL B	1.78	2.94	0.80	1.82	 		20-22 [0.50-0.35mm ²]	1924955-3
2.06 MAX	DETAIL A	1.78	2.94	1.00	1.96	 		18 [0.75mm ²]	1924955-2
1.5 - 1.85	DETAIL A	1.78	2.94	0.80	1.82	 		20-22 [0.50-0.35mm ²]	1924955-1
INSULATION DIAMETER	REELING	M	L	K	J	FINISH	MATERIAL	WIRE SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±"

1 PLC ±.15

2 PLC ±"

3 PLC ±"

4 PLC ±"

ANGLES ±"

FINISH

SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

F. KINSEY

17DEC2007

CHK

F. KINSEY

17DEC2007

APVD

J. MYER

17DEC2007

PRODUCT SPEC

108-2296

APPLICATION SPEC

114-13183

WEIGHT

-

CUSTOMER DRAWING

NAME

CONTACT, 0.64mm, FEMALE, GENERATION Y, UNSEALED APPLICATIONS

SIZE

A1

CAGE CODE

00779

DRAWING NO

1924955

RESTRICTED TO

-

SCALE

15:1

SHEET

2

OF

2

REV

C

4805 (3/13)