






P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	PART STATUS CHANGE TO DISCONTINUNACE	19JUN2026	NS	PS



SCALE 2:1
1986825-4 AS SHOWN



1. MATERIAL:
HOUSING - PA (PLYAMIDE) ,UL94 V0, COLOR - GREEN
PUSH BUTTON- PA (POLYAMIDE), COLOR - ORANGE
CLAMPING SPRING - STAINLESS STEEL
PIN - COPPER ALLOY(CuCr) -BRIGHT TIN PLATED,
OVER NICKEL UNDERPLATE

2. MECHANICAL:
MIN. PC BOARD HOLES DIAMETER : 1.2 mm
MAX. PC BOARD THICKNESS : 2.4 mm
WIRE STRIPPING LENGTH : 11 mm

3. ELECTRICAL:
WIRE RANGE : 12-30 AWG (2.5mm2 TO 0.2mm2)
RATED VOLTAGE : 300V
RATED CURRENT : 15A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

	62.46	12	1-1986775-2
	57.38	11	1-1986775-1
	52.30	10	1-1986775-0
OBSOLETE	47.22	9	1986775-9
	42.14	8	1986775-8
OBSOLETE	37.06	7	1986775-7
	31.98	6	1986775-6
OBSOLETE	26.90	5	1986775-5
	21.82	4	1986775-4
	16.74	3	1986775-3
	11.66	2	1986775-2
	DIM "L"	POLE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12OCT2012 KIRAN HOLAL	 TE Connectivity		
DIMENSIONS: mm		CHK 12OCT2012 MARK BRUBAKER			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 12OCT2012 MARK BRUBAKER	NAME SPRING TYPE, SIDE WIRE ENTRY TERMINAL BLOCK PITCH 5.08MM		
0 PLC ±° 1 PLC ±0.5 2 PLC ±0.25 3 PLC ±° 4 PLC ±° ANGLES ±1°		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL		APPLICATION SPEC	A300779C-1986775		
FINISH		WEIGHT	SCALE 1:4 SHEET 1 OF 1 REV C1		
		CUSTOMER DRAWING			