






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12MAY2022	SD	MM
	B	ECN-23-234640	11OCT2023	CD	CD

NOTES:

- 1 MATERIALS AND FINISH:
- HOUSING, LEVER, COVER: PBT
- SPRING CONTACT: STAINLESS STEEL
- CONTACTS: COPPER ALLOY, TIN PLATED
- SCREW: STEEL, ZINC PLATED
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING
- 4 SOLID AND STRANDED WIRE ONLY: 12-18AWG
MAX INSULATION OD: Ø4.2
STRIP LENGTH: 13.00±0.50
- 5 SOLID AND STRANDED WIRE ONLY: 6-14AWG
MAX INSULATION OD: Ø6.0
STRIP LENGTH: 13.00±0.50
- 6 COMBINATION SLOTTED PHILIPS SCREW. TORQUE 0.8-1.2 N·m.



2382635-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. LATORRE 04FEB2021	TE Connectivity			
		CHK M. MOSTOLLER 04FEB2021				
DIMENSIONS:		APVD -	NAME LUMAWISE TB POWER INPUT TERMINAL BLOCK			
mm		PRODUCT SPEC 108-160129	SIZE A2		CAGE CODE 00779	DRAWING NO C-2382635
		APPLICATION SPEC 114-160073			RESTRICTED TO -	
MATERIAL		WEIGHT -				
		CUSTOMER DRAWING	SCALE 2:1		SHEET 1 OF 1	REV B