



CONNECTOR OVERALL DIMENSIONS WITH COVER KIT AND LEVER ASSEMBLED





VIEW FROM WIRE INSERTION SIDE		CAVITIES POSITION	
		CONTACT P/N	POSITION
		968220-1 & 968221-1	8 to 28; 30 to 50; 52 to 72; 74 to 94
		1452158-1 & 1241608-1	7, 29, 51, 73
		1241394-1 & 1241396-1	1 to 6

-	1	PA6.6 GF30	YELLOW	C.P.A.	6
1	1	PA6.6 GF13	BLACK	COVER	5
1	1	PA6.6 GF30	BLACK	LEVER	4
1	1	PA6 GF30	VIOLET	SECONDARY LOCK 6 POSN.	3
1	1	PA6 GF30	VIOLET	SECONDARY LOCK 88 POSN.	2
1	1	PBT+ASA-GF20/PA66 GF30 PBT GF15 / PA66 GF25 SILICON	BLACK/LIGHT BROWN:HOUSING YELLOW:PERIPHERAL SEAL RED-BROWN:FAMILY SEAL	CARRIER HSG.	1
QTY.	QTY.	MATERIALS	COLOURS	DESCRIPTION	ITEM
284743-2 (NOTE 6)	284743-1 (NOTE 5)	PART-NO.			
G	G	REV			


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E4	ECR-14-008540	06SEP2014	M.G.	M.G.
	E5	REVISED PER ECO-18-014477	12SEP2018	AP	VN
	F	ECN-21-126823	18NOV2021	VN	VN
	G	REVISED PER ECN-25-309621	05MAR2025	V.N.	V.N.

P/N 284743-1 AS SHOWN
FIAT VERSION



- 1) CONNECTOR IS SUITABLE TO BE MATED WITH COUNTERPART P/N 284617-1
- 2) CONNECTOR CAVITIES ARE SUITABLE FOR CONTACTS:
- 0.64 MQS Clean Body contact WSR 0.35±0.50 mm² P/N 1703296-1 (FIAT restricted version)
(Minimum insulation diameter: 1.2 mm; Maximum isolation diameter: 1.6 mm)
 - 0.64 MQS Clean Body contact WSR 0.35 mm² P/N 968220-1
(Minimum insulation diameter 1.2 mm; Maximum isolation diameter: 1.3 mm)
 - 0.64 MQS Clean Body contact WSR 0.75 mm² P/N 1703298-1 (FIAT restricted version)
(Minimum insulation diameter 1.7 mm; Maximum isolation diameter: 1.9 mm)
 - 0.64 MQS Clean Body contact WSR 0.50±0.75 mm² P/N 968221-1
(Minimum insulation diameter 1.4 mm; Maximum isolation diameter: 1.9 mm)
 - 1.5 MQS Clean Body contact WSR 0.50 mm² P/N 1452158-1
(Minimum insulation diameter 1.4 mm; Maximum isolation diameter: 1.6 mm)
 - 1.5 MQS Clean Body contact WSR 0.75±1.50 mm² P/N 1241608-1
(Minimum insulation diameter 1.7 mm; Maximum isolation diameter: 2.4 mm)
 - 2.8K MCP Contacts SWS, WSR 0.35 mm² P/N 1241392-1
(Minimum insulation diameter 1.2 mm; Maximum isolation diameter: 1.3 mm)
 - 2.8K MCP Contacts SWS, WSR 0.5±1.0 mm² P/N 1241394-1
(Minimum insulation diameter 1.4 mm; Maximum isolation diameter: 2.1 mm)
 - 2.8K MCP Contacts SWS, WSR > 1.0±2.5 mm² P/N 1241396-1
(Minimum insulation diameter 2.0 mm; Maximum isolation diameter: 3.0 mm)
- SINGLE WIRE SEAL FOR MCP 2.8K:
P/N 963294-1 FOR WSR 0.35-1.0 mm²;
P/N 963293-1 FOR WSR 1.5 mm²;
P/N 963292-1 FOR WSR 2.5 mm².

- 3) TO CLOSE UNUSED CAVITIES:
- P/N 284583-1 for MQS Clean Body contacts cavities
 - P/N 1394872-1 for 1.5 mm Clean Body contact cavities
 - P/N 828922-1 for 2.8K MCP contact cavities
- 4) ITEM 2, 3 AND 4 ARE SUPPLIED NOT ASSEMBLED IN THE SAME PACKAGE.
- 5) ITEMS 5 AND 6 ARE SUPPLIED PRE-ASSEMBLED, IN THE SAME PACKAGE.
- 6) ITEMS 5 IS SUPPLIED NOT ASSEMBLED IN THE SAME PACKAGE
ITEM 6 IS NOT SUPPLIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.BISETTI CHK O.CANUTO	03OCT2001 03OCT2001	 TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	PRODUCT SPEC 108-20235	NAME CONNECTOR HOUSING, 94 POS. MQS , 1.5 mm Clean body, MCP 2.8 + COVER AND C.P.A. KIT	
	0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ± 4 PLC ± ANGLES ±30°	APPLICATION SPEC 411-20067	WEIGHT -	SIZE A2	CAGE CODE 0779
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING	SCALE 2:1	SHEET 1	OF 1
				REV G	