

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2005



© COPYRIGHT 2005

BY -


ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	M6	REVISED PER ECR-18-010208	31JUL2018	BDA	SF
	M7	REVISED PER ECN-26-399116	11AUG2026	DS	RB



A-A



B-B



NOTES:

Bemerkungen:



2-6 µm Sn OVER Ni IN CRIMP-AREA
2-6 µm Sn über Ni in der Crimpzone




0.8 µm Au OVER Ni IN CONTACT-AREA
0.8 µm Au über Ni in der Kontaktzone

3

SUITABLE FOR Ø1.0-2.5mm
Für Isolations Ø1.0-2.5mm geeignet




0.8 µm Au OVER 1.3 µm Ni ON INSIDE OF WIRE BARREL AND CONTACT AREA
0.8 µm Au über 1.3 µm Ni in der Drahtcrimp und Kontaktzonen, sonst 1.3 µm Ni



	107-3, FIG.2		926882-8	BRASS	PRE-TIN
SUPERSEDED BY 350536-7	107-3, FIG.1	926893-7	926884-7	BRASS	 
SUPERSEDED BY 350536-6	107-3, FIG.1	926893-6	926884-6	PHOS BRONZE	 
OBSOLETED	107-3, FIG.1	926893-5	926882-5	COPPER ALLOY	PRE-TIN
OBSOLETED	107-3, FIG.1	926893-4	926882-4	COPPER ALLOY	PLAIN
	107-3, FIG.1	926893-3	926882-3	PHOS BRONZE	PRE-TIN
SUPERSEDED BY 350536-2	107-3, FIG.1	926893-2	926882-2	BRASS	
	107-3, FIG.1	926893-1	926882-1	BRASS	PRE-TIN
	REELING	LOOSE PIECE	PART NO.	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.Skoda 29NOV2005	 TE Connectivity		
		CHK R.Vlcek			
		APVD M.Bleicher			
		PRODUCT SPEC 108-1031			
		APPLICATION SPEC 114-18011	NAME UNIVERSAL MNL Socket 0.5-2.1 mm SQUARE WIRE RANGE		
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-926882
		CUSTOMER DRAWING			RESTRICTED TO
		SCALE 5:1			SHEET 1 OF 1
					REV M7

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.2
	1 PLC ±0.2
	2 PLC ±0.2
	3 PLC ±
	4 PLC ±
	ANGLES ±1°
MATERIAL SEE TABLE	FINISH SEE TABLE