





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B4	REVISED PER ECR-26-285663	17JUL2026	BN	YZ

SECT.
断面 A-ASECT.
断面 B-B

この寸法はかん合力によって規定する。

THIS DIMENSION IS CONTROLLED WITH MATING FORCE

SECT.
断面 C-C

NOTE;

- STRESS RELIEVING FINISH IS SUBJECT TO CHANGE BY THE TYPE OF STRESS RELIEVING PROCESS
INERT GAS FURNACE - - - - MATTE
ATMOSPHERIC FURNACE FOLLOWED BY ACID PICKLE - - - - BRIGHT
- CONTACT INSERTION FORCE : 39.2N MAX.
CONTACT EXTRACTION FORCE : 4.9 - 39.2N
- APPLICATION FEED : 21.49mm
- ADD THE INTERLEAVING PAPER



TIN PLATING	BRASS THICKNESS 0.32mm	170384-4
— # —	BRASS THICKNESS 0.32mm	170384-3
TIN PLATING	BRASS THICKNESS 0.32mm	170384-2
— # —	BRASS THICKNESS 0.32mm	170384-1
FINISH	MATERIAL	PART NO.


WIRE RANGE 0.3~0.5mm ² (AWG#22-20)	INSULATION DIA 1.5~2.2mmφ
--	------------------------------

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

10以下	± 0.2
10を超え30以下	± 0.25
30を超え100以下	± 0.3
ANGLES	± 3°



DWN	J.SATO	17MAY2007
CHK	S.MANABE	17MAY2007
APVD	S.MANABE	17MAY2007
PRODUCT SPEC		

APPLICATION SPEC

WEIGHT

0.000000

MATERIAL

SEE TABLE

FINISH

SEE TABLE

TE

TE Connectivity

NAME

.250 SERIES RECEPTACLE WITHOUT LATCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-170384

—

CUSTOMER DRAWING

SCALE

4:1

SHEET

1 OF 1

REV B4