

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	PART STATUS CHANGE TO DISCONTINUNACE	22JUL2026	NS	PS




MATERIAL:
HOUSING: POLYAMIDE 66, UL94V-0, COLOR: BLACK
TERMINAL: BRASS, TIN PLATED
SCREW: STEEL, NICKEL PLATED

ELECTRICAL:
CURRENT RATING: 15A, 300V
INSULATION WITHSTANDS: 2000V, 1 MIN
INSULATION RESISTANCE: 2000Mohm, 500VDC
WIRE RANGE: 16-22 AWG

ENVIRONMENTAL:
OPERATION TEMP.: -40° TO +105° C
SCREW TORQUE: 12 LB-IN

1. RECOMMENDED STACKING NOT TO EXCEED 16 POSITIONS.

OBSOLETE	123.75	132.00	16	1-1977477-6
OBSOLETE	115.50	123.75	15	1-1977477-5
OBSOLETE	107.25	115.50	14	1-1977477-4
OBSOLETE	99.00	107.25	13	1-1977477-3
OBSOLETE	90.75	99.00	12	1-1977477-2
OBSOLETE	82.50	90.75	11	1-1977477-1
OBSOLETE	74.25	82.50	10	1-1977477-0
OBSOLETE	66.00	74.25	9	1977477-9
OBSOLETE	57.75	66.00	8	1977477-8
OBSOLETE	49.50	57.75	7	1977477-7
OBSOLETE	41.25	49.50	6	1977477-6
OBSOLETE	33.00	41.25	5	1977477-5
	24.75	33.00	4	1977477-4
	16.50	24.75	3	1977477-3
	8.25	16.50	2	1977477-2
	DIM B	DIM A	NO OF POS	PART NUMBER



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 16SEP2008	TE Connectivity		
		CHK S MACE 9/16/08			
DIMENSIONS: mm		APVD S MACE 9/16/08	NAME DUAL BARRIER, TERMINAL BLOCK 8.25mm PITCH		
		PRODUCT SPEC			
		APPLICATION SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT 0.000000	SIZE A3	CAGE CODE 00779	DRAWING NO C-1977477
MATERIAL -		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
				REV B2	