


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	PART STATUS CHANGE TO DISCONTINUNACE	21JUL2026	NS	PS

MATERIALS:
HOUSING: PA66, UL94V-0, COLOR: GREEN.
CONTACT: PHOS BRONZE, TIN PLATED.
WIRE GUARD: STEEL, ZINC CHROMATE.
CAGE CLAMP: STEEL, ZINC CHROMATE.
SCREW: STEEL, ZINC PLATED.


ELECTRICAL:
VOLTAGE RATING: 300V.
CURRENT RATING: 16A.
INSULATION RESISTANCE 2000Mohm/DC500V.
WITHSTANDING VOLTAGE AC2000V MIN
WIRE RANGE: 14-24 AWG

MECHANICAL:
SCREW TORQUE: 7.0 IN-LB
WIRE STRIP LENGTH: 10mm


ENVIRONMENTAL:
WORKING TEMP.: -40°C TO +105°C.





2-1986484-5 IS OBSOLETE



2-1986484-6 IS OBSOLETE



5.08±0.10 2.54±0.30



SEE DETAIL

SEE DETAIL

121.92±0.5	24	2-1986484-4
116.84±0.5	23	2-1986484-3
111.76±0.5	22	2-1986484-2
106.68±0.5	21	2-1986484-1
101.60±0.5	20	2-1986484-0
96.52±0.5	19	1-1986484-9
91.44±0.5	18	2-1986484-6
91.44±0.5	18	1-1986484-8
86.36±0.5	17	1-1986484-7
81.28±0.5	16	1-1986484-6
76.20±0.5	15	1-1986484-5
71.12±0.5	14	1-1986484-4
66.04±0.5	13	1-1986484-3
60.96±0.5	12	1-1986484-2
55.88±0.5	11	1-1986484-1
50.80±0.5	10	1-1986484-0
45.72±0.5	9	1986484-9
40.64±0.5	8	1986484-8
35.56±0.5	7	1986484-7
30.48±0.5	6	1986484-6
25.40±0.5	5	2-1986484-5
25.40±0.5	5	1986484-5
20.32±0.5	4	1986484-4
15.24±0.5	3	1986484-3
10.16±0.5	2	1986484-2
DIM L	NO OF POS	PART NUMBER

1 NOTE DELETED

2 PART MARKED WITH BLACK PERMANENT MARKING

3 OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 17NOV2008	 TE Connectivity		
DIMENSIONS: mm		CHK C RICHARD 11/17/08			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 11/17/08	NAME		
0 PLC ± - 1 PLC ± 0.2 2 PLC ± 0.10 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC	TERMINAL BLOCK, PLUG, 5.08mm PITCH		
MATERIAL		FINISH	SIZE	CAGE CODE	DRAWING NO
-		-	A3	00779	C-1986484
CUSTOMER DRAWING		SCALE	NTS	SHEET	1 OF 1
		REV	A3		