





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	PCN-25-266608	08AUG2026	GSK	CAS



RECOMMENDED PANEL CUTOUT



DETAIL F

- 1 CAVITY IDENTIFICATION CHARACTERS ON FRONT AND REAR FACE.
2. RECEPTACLE WILL ACCEPT 3 TYPE XII PIN CONTACTS.
3 5.08μm [.000200] MIN NICKEL OVER 10.16μm [.000400] MIN COPPER.

OBSOLETE	PER DETAIL F	NO	208495-4
OBSOLETE	AS SHOWN	YES	208495-2
	AS SHOWN	NO	208495-1
	FRONT FACE CONFIGURATION	PERIPHERAL SEAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 1-29-92 W.G.LENKER	TE Connectivity	
DIMENSIONS: INCHES		CHK 2-11-92 D.STONE		
		APVD 2-12-92 K.BEAVER	NAME RECEPTACLE ASSEMBLY, 22-3, STD SEX, CMC	
		PRODUCT SPEC		
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
		FINISH	A2 00779 C-208495	
MATERIAL RECEPTACLE: THERMOPLASTIC, BLACK		RCPT SHELL: 3 PIN: NICKEL PLATED	RESTRICTED TO	
		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1