





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	PART STATUS CHANGE TO DISCONTINUANCE	07JUL2026	NS	PS



- NOTES:
- MATERIALS & FINISH
HOUSING : PA6.6 , UL94 V0, COLOR -GREEN
SCREW M3 : BRASS, NICKEL PLATED
CLAMP : BRASS, NICKEL PLATED
CONTACT : PHOSPHOR BRONZE , TIN PLATED
 - RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE No. E60677.
 - IMQ CERTIFICATE WITH SURVEILLANCE ON CONFORMITY WITH IEC 998-1/998-2-1.
 - NOT CUMULATIVE TOLERANCE.
 - MECHANICAL
INSERTION FORCE PER POLE : MAX 3N
WITHDRAWAL FORCE PER POLE : MIN 1.5 N
RECOMMENDED/ HIGHEST TIGHTENING TORQUE:0.5/0.6 Nm
WIRE STRIPPING LENGTH: 6.0 TO 7.5mm
 - ELECTRICAL
WIRE RANGE : 30 - 12 AWG
MAX. VOLTAGE : 300 V
MAX CURRENT : 15 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : > 1000 M Ohm (500V DC)
 - OPERATING TEMPERATURE RANGE: -40°C TO +110°C



POLARIZATION KEY SLOT



OBSOLETE	59.8	55.0	10	I-796858-0
	54.8	50.0	9	796858-9
	49.8	45.0	8	796858-8
	44.8	40.0	7	796858-7
	39.8	35.0	6	796858-6
	34.8	30.0	5	796858-5
	29.8	25.0	4	796858-4
	24.8	20.0	3	796858-3
	19.8	15.0	2	796858-2
	L	H	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 12FEB2001	TE Connectivity	
DIMENSIONS: mm		CHK D. BIEVENOUR 12FEB2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 12FEB2001	NAME TERMINAL BLOCK, PLUG, 90 DEG, WITH SCREW LOCKING FLANGE 5.00mm PITCH	
0 PLC ± 1 PLC ±0.2 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2° FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
MATERIAL		SIZE A200779	CAGE CODE C-796858	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV B2