


[Click here](#) for the 3D model.

**General Information**

Series	T356
Dielectric	MnO <sub>2</sub> Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Conformal, Dipped
Features	Low Leakage, Reverse Voltage
RoHS	Yes
Termination	Tin
AEC-Q200	No
Construction	Conformal
Notes	Longest Lead Is Positive.

**Dimensions**

D	5.5mm	Capacitance	10 uF
H	10.2mm	Tolerance	10%
S	5.08mm +/-0.38mm	Voltage DC	25 VDC (85C), 16 VDC (125C), 0.25 VDC (125C Reverse)
LL	4.75mm +/-0.81mm	Temperature Range	-55/+125°C
F	0.5mm +/-0.05mm	Dissipation Factor	6%
		Leakage Current	2 uA

**Packaging Specifications**

Packaging	Bulk, Bag
Packaging Quantity	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.