




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER ECR-26-286663	30JUL2026	GSK	CAS




RECOMMENDED PANEL CUTOUT



1. HOUSING: THERMOPLASTIC, BLACK.
THREADED INSERTS: BRASS
2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
3. WILL ACCEPT NINE (9) MULTIMATE PIN CONTACTS.

OBSOLETE	YES	211767-3
	YES	211767-2
	NO	211767-1
	4-40 THREADED INSERTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.BROCKWAY 09-28-94	 TE Connectivity							
		CHK R.STONE 09-30-94								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RCPT HSG, STD SEX, VDE, SHELL SIZE 17, CPC —						
		APVD —						NAME		
		PRODUCT SPEC —								
		APPLICATION SPEC —								
MATERIAL		FINISH		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-211767	RESTRICTED TO —		
		—		CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV G