
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
G	14

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECO–14–003457	11MAR2014	NK	DR



1. STAMPED AMP 16–14*, APPROX AS SHOWN.
2. FOR .115 TO .170 WIRE INSULATION DIA.
3. TONGUE MATERIAL THK IS .031±.002.
4. NOTE DELETED

QTY	PACKAGE TYPE	PART NO	MATERIAL & FINISH
5000	ON TAPE, REEL	2–327748–1	BODY: COPPER PER ASTM B152 TIN PLATE PER ASTM B545 SLEEVE: COPPER PER ASTM B152 TIN PLATE PER ASTM B545 INSULATION: NYLON, COLOR – BLUE
1000	LOOSE PIECE	327748	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± .008
4 PLC	± –
ANGLES	± 5°

MATERIAL: –

FINISH: –

DWN	JR RUTH	03APR01
CHK	MS FEHER	03APR01
APVD	T MICHIELUTTI	03APR01
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME: WIRE TERMINAL, PIDG, RECTANGULAR TONGUE, WIRE SIZE: 16–14

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–327748	—

CUSTOMER DRAWING

SCALE	SHEET	REV
8:1	1 OF 1	G1