




P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




DETAIL A-A




DETAIL P1




DETAIL P2




DETAIL P3




DETAIL D




DETAIL E




DETAIL N




DETAIL P




DETAIL S




DETAIL F




DETAIL R




DETAIL T




DETAIL G




DETAIL V




DETAIL M




DETAIL H




DETAIL W




DETAIL J




DETAIL X



DETAIL Y




DETAIL K




DETAIL Z

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 18OCT2000	 TE Connectivity	
		CHK D. BIEVENOUR 18OCT2000		
DIMENSIONS: mm		APVD D. BIEVENOUR 18OCT2000	NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH	
		PRODUCT SPEC		
MATERIAL SEE NOTES	SEE NOTES	APPLICATION SPEC	SIZE A100779	DRAWING NO C=796634
		WEIGHT		
		CUSTOMER DRAWING	SCALE 4:1	SHEET 2 OF 3
			REV R14	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DETAIL AB



DETAIL AC

OBSOLETE	NICKEL	TIN	 	DETAIL AC	25.40	5	8-796634-5
	CLAMP PLATING	CONTACT PLATING	MARKING	SPECIAL	L	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm  TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±. 4 PLC ±. ANGLES ±2° FINISH MATERIAL SEE NOTES SEE NOTES				DWN S.WELDON 18OCT2000 CHK D.BIEVENOUR 18OCT2000 APVD D.BIEVENOUR 18OCT2000 PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING	NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH		
				SIZE A CAGE CODE 00779 DRAWING NO C=796634 RESTRICTED TO -	SCALE 5:1	SHEET 3 OF 3	REV R 14