


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-26-282233	01JUL2026	GSK	MP




1 BODY MATERIAL THK 1.447±0.051[.057±.002]

2 FOR ø11.887[ø.468] MAX WIRE INS.

3 STAMP AMP 2* APPROX AS SHOWN.

4 MATERIAL:
BODY – COPPER PER ASTM B152
INSULATION – NYLON

5 FINISH:
BODY – TIN PLATE .000100 [0.00254]
MIN EXT PER ASTM B545
INSULATION – RED



50	LOOSE PC	328655
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S.S. GOULDEN 6-21-93		 TE Connectivity									
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: -		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		APVD B. BARE 6-21-93		NAME TERMINAL, RING TONGUE, TERMINYL WIRE SIZE: 2 AWG							
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 26.7-42.4mm ² [52,600-83,700] STRANDED				PRODUCT SPEC 108-162357		APPLICATION SPEC -		SIZE A3		CAGE CODE 00779	DRAWING NO C-328655	RESTRICTED TO -			
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 		FINISH 		WEIGHT				CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV E