






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
H		REVISED PER ECR-24-213594	03JUL2024	RK	FJS


- 1 WIRE RANGE: 0.13–0.2mm² (26–24 AWG).
- 2 INSULATION RANGE: 0.64–1.27 [.025–.050] MAX. DIA.
- 3 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4 TIP PLATE WITH 0.00076–0.00091 [.000030–.000036] MIN PRECIOUS METAL PLATE IN THE LOCALIZED PRECIOUS METAL PLATE AREA OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.



SECTION A—A
SCALE 10:1



SECTION B—B
SCALE 10:1



SECTION C—C
SCALE 10:1

METRIC

PRECIOUS METAL PLATE	0.20 [.008] PHOS BRZ	350968–2
PRE–TIN	0.20 [.008] PHOS BRZ	350968–1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 3–21–95	TE Connectivity	
		CHK R. SWING 3–21–95		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. LONG 3–21–95	NAME	
	0. PLC ± –	PRODUCT SPEC	MR PIN	
	1. PLC ± –	APPLICATION SPEC	—	
MATERIAL SEE TABLE	2. PLC ± 0.13 [.005]	WEIGHT	SIZE	CAGE CODE
	3. PLC ± –	—	A1	00779
	4. PLC ± –	—	C=	350968
	ANGLES ± –	—	RESTRICTED TO	—
CUSTOMER DRAWING		SCALE	5:1	SHEET 1 OF 1