


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K3	ECR-25-239014	28APR2025	ABS	PS



10 OBSELETE	9	2	2.59	1.295	1-103653-1	12	6-103949-1
10 OBSELETE	9	2	2.39	1.195	1-103653-0	1 1	6-103949-0
OBSELETE	9	2	2.19	1.095	103653-9	10	5-103949-9
	9	2	1.99	.995	103653-8	9	5-103949-8
	9	2	1.79	.895	103653-7	8	5-103949-7
	9	3	2.39	.795	103653-6	7	5-103949-6
	9	2	1.39	.695	103653-5	6	5-103949-5
	9	4	2.38	.595	103653-4	5	5-103949-4
	9	4	1.98	.495	103653-3	4	5-103949-3
	9	5	1.98	.395	103653-2	3	5-103949-2
10 OBSELETE SUPERSEDED BY 5-103949-9 SUPERSEDED BY 5-103949-8 OBSELETE SUPERSEDED BY 5-103949-6 SUPERSEDED BY 5-103949-5 SUPERSEDED BY 5-103949-4 SUPERSEDED BY 5-103949-3 SUPERSEDED BY 5-103949-2 SUPERSEDED BY 5-103949-1	9	8	2.36	.295	103653-1	2	5-103949-1
	8	2	2.59	1.295	1-103653-1	12	1-103949-1
	8	2	2.39	1.195	1-103653-0	1 1	1-103949-0
	8	2	2.19	1.095	103653-9	10	103949-9
	8	2	1.99	.995	103653-8	9	103949-8
	8	2	1.79	.895	103653-7	8	103949-7
	8	3	2.39	.795	103653-6	7	103949-6
	8	2	1.39	.695	103653-5	6	103949-5
PLATING	8	4	2.38	.595	103653-4	5	103949-4
	8	4	1.98	.495	103653-3	4	103949-3
	8	5	1.98	.395	103653-2	3	103949-2
	8	8	2.36	.295	103653-1	2	103949-1
	6						
	B						
	A						
	HOUSING PART NUMBER					NO OF POSN	ASSEMBLY PART NUMBER ON STRIP

- 1

 CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2

 USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3

 THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4

 POINT OF MEASUREMENT FOR PLATING THICKNESS
5. FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103894
- 6

 ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7

 MATERIAL- HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK
PINS: PHOS. BRONZE
- 8

 FINISH- PINS: .000030 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, OVER .000050 NICKEL.
- 9

 FINISH- PINS: .000030 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, OVER .000050 NICKEL.
- 10

 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 26JUL00	TE Connectivity				
		CHK K WRIGHT 26JUL00					
		APVD K WRIGHT 26JUL00					
		PRODUCT SPEC 108-25034					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH SEE TABLE	APPLICATION SPEC 114-25026		NAME SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, POLARIZED, W/ LATCH WINDOWS, FOR #26-#30 AWG WIRE SIZE, STRIP FORM		
MATERIAL 7		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=103949	RESTRICTED TO -	
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 of 1	REV K3