



REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	J2	ECR-25-239014	26APR2025	ABS	PS

D

C

B

A



- 1 CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2 USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3 THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103655
- 6 ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7 PINS:.000015 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 8 PINS:.000015 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT IDENTIFICATION
LETTER "D" (LOCATED
IN THIS AREA)

HOUSING (SEE
TABLE FOR PART NO)

POSITION #1 INDICATOR
(FARSIDE)

OBSOLETE 9	8	2	2.40	1.198	1-104503-1	12	6-103951-1	
		2	2.20	1.098	1-104503-0	11	6-103951-0	
		2	2.00	.998	104503-9	10	5-103951-9	
		2	1.80	.898	104503-8	9	5-103951-8	
		2	1.60	.798	104503-7	8	5-103951-7	
		2	1.40	.698	104503-6	7	5-103951-6	
		4	2.39	.598	104503-5	6	5-103951-5	
		4	1.99	.498	104503-4	5	5-103951-4	
		5	1.99	.398	104503-3	4	5-103951-3	
		5	1.49	.298	104503-2	3	5-103951-2	
		10	1.98	.198	104503-1	2	5-103951-1	
OBSOLETE 9	7	2	2.40	1.198	1-104503-1	12	4-103951-1	
		2	2.20	1.098	1-104503-0	11	4-103951-0	
		2	2.00	.998	104503-9	10	4-103951-9	
		2	1.80	.898	104503-8	9	4-103951-8	
		2	1.60	.798	104503-7	8	4-103951-7	
		2	1.40	.698	104503-6	7	4-103951-6	
		4	2.39	.598	104503-5	6	4-103951-5	
		4	1.99	.498	104503-4	5	4-103951-4	
		5	1.99	.398	104503-3	4	4-103951-3	
		5	1.49	.298	104503-2	3	4-103951-2	
SUPERSEDED BY 5-103951-4		10	1.98	.198	104503-1	2	4-103951-1	
OBSOLETE								
SUPERSEDED BY 5-103951-1								
		PLATING	6	B	A	HOUSING PART NUMBER	NO OF POSN PER ASSY	ASSEMBLY PART NUMBER ON STRIP

SUPERSEDED BY 5-103951-4

OBSOLETE
SUPERSEDED BY 5-103951-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. MAYER 11-5-86	TE Connectivity				
DIMENSIONS: INCHES		CHK P.C.deYONG 11-12-86					
		APVD P.C.deYONG 11-12-86	NAME				
		PRODUCT SPEC 108-25034	PIN ASSEMBLY, AMPMODU MTE, SINGLE ROW, .100, WITH GUIDE RIBS, FOR #22-#26 AWG WIRE SIZE, STRIP FORM				
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR:BLACK PINS: PHOS BRONZE		FINISH SEE TABLE	114-25026	APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=103951
			WEIGHT -		SCALE 4:1	SHEET 1 OF 1	REV J2
			CUSTOMER DRAWING				