








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	REDRAWN/REVISED PER ECO-17-001757	07NOV2017	GR	JO
	U1	PN 7-104192-6 OBSOLETE	02JAN2026	KS	PS



SCALE 8:1

- 1 CONTACT AREAS PLATED WITH 0.76µm GOLD,SOLDER TAILS PLATED WITH 3.81µm TIN-LEAD,ALL OVER 1.27µm NICKEL
- 2 NOTE DELETED.
- 3 NOTE DELETED.
- 4 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 5 CONTACT AREAS PLATED WITH 0.76µm GOLD,SOLDER TAILS PLATED WITH 3.81µm TIN,ALL OVER 1.27µm NICKEL
- 6 NOTE DELETED.
- 7 FINISH: 0.03µm MIN GOLD ON GOLD PLATED AREA, 3.81µm MATTE IN TIN-LEAD ON TIN PLATED AREA, UNDER PLATING: 1.27µm NICKEL ON ENTIRE CONTACT.
- 8 FINISH: 0.03µm MIN GOLD ON GOLD PLATED AREA, 3.81µm MATTE IN TIN ON TIN PLATED AREA, UNDER PLATING: 1.27µm NICKEL ON ENTIRE CONTACT
- 9 NOTE DELETED.
- 10 MATERIAL- HOUSING:LCP
COLOR:BLACK
POST:COPPER ALLOY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. RAMESH	07NOV2017	TE Connectivity	
		CHK J. OLSON	07NOV2017		
DIMENSIONS:		APVD J. OLSON	07NOV2017	NAME	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		RECEPTACLE ASSEMBLY,VERTICAL, SINGLE ROW, AMPMODU System 50	
		PRODUCT SPEC		-	
		108-1093		-	
		APPLICATION SPEC		-	
		114-25031		-	
MATERIAL		WEIGHT		-	
SEE DETAIL		CUSTOMER DRAWING		-	
10		SCALE		4:1	
		SHEET		1 OF 2	
		REV		U1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

8	31.75	25	34.14	26	8-104192-0	OBSOLETE
	15.24	13	17.63	13	7-104192-9	
	5.08	4	7.47	5	7-104192-8	
	36.83	29	39.22	30	7-104192-7	
	30.48	24	32.87	25	7-104192-6	
	24.13	19	26.52	20	7-104192-5	
	17.78	14	20.17	15	7-104192-4	
	13.97	11	16.36	12	7-104192-3	
	11.43	9	13.82	10	7-104192-2	
5	8.89	7	11.28	8	7-104192-1	
	31.75	25	34.14	26	6-104192-0	
	15.24	13	17.63	13	5-104192-9	
	5.08	4	7.47	5	5-104192-8	
	36.83	29	39.22	3	5-104192-7	
	30.48	24	32.87	25	5-104192-6	
	24.13	19	26.52	20	5-104192-5	
	17.78	14	20.17	15	5-104192-4	
	13.97	11	16.36	12	5-104192-3	
	11.43	9	13.82	10	5-104192-2	
	8.89	7	11.28	8	5-104192-1	
FINISH	DIM_C	^B SPACES	DIM_A	NO OF POSN	PART NUMBER	

7	31.75	25	34.14	26	3-104192-0	
	15.24	13	17.63	13	2-104192-9	
	5.08	4	7.47	5	2-104192-8	
	36.83	29	39.22	30	2-104192-7	
	30.48	24	32.87	25	2-104192-6	
	24.13	19	26.52	20	2-104192-5	
	17.78	14	20.17	15	2-104192-4	
	13.97	11	16.36	12	2-104192-3	
	11.43	9	13.82	10	2-104192-2	
1	8.89	7	11.28	8	2-104192-1	
	31.75	25	34.14	26	1-104192-0	
	15.24	13	17.63	13	104192-9	
	5.08	4	7.47	5	104192-8	
	36.83	29	39.22	3	104192-7	
	30.48	24	32.87	25	104192-6	
	24.13	19	26.52	20	104192-5	
	17.78	14	20.17	15	104192-4	
	13.97	11	16.36	12	104192-3	
	11.43	9	13.82	10	104192-2	
	8.89	7	11.28	8	104192-1	
FINISH	DIM_C	^B SPACES	DIM_A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
G.RAMESH

07NOV2017

CHK
J.OLSON

07NOV2017

APVD
J.OLSON

07NOV2017

TE Connectivity

NAME
RECEPTACLE ASSEMBLY,VERTICAL,
SINGLE ROW, AMPMODU System 50

DIMENSIONS:
mm

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±0.3
±0.13
±
±
±0.5°

SEE DETAIL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC
108-1093
APPLICATION SPEC
114-25031
WEIGHT
-

CUSTOMER DRAWING

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=104192

RESTRICTED TO
-

SCALE
4:1

SHEET
2

OF
2

REV
U1

4805 (3/13)