





REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
AA1		ECN-23-194687	19JAN2023	RK	MF
AA2		PN 1-104477-1 OBSOLETE	03JAN2026	KS	PS

D




- CONTACT AREAS PLATED WITH 0.76µm GOLD, SOLDER TAILS PLATED WITH 3.81µm TIN-LEAD, ALL OVER 1.27µm NICKEL
- NOTE DELETED.
- CIRCUIT IDENTIFICATION FEATURE OMITTED ON 8, 10, 12, & 14 POSITION HEADER ASSEMBLIES
- DIMENSIONS APPLIES AT BASE OF SHROUD
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- NOTE DELETED.
- CONTACT AREAS PLATED WITH 0.76µm GOLD, SOLDER TAILS PLATED WITH 3.81µm TIN, ALL OVER 1.27µm NICKEL.
- HOUSING: LCP, COLOR: BLACK
POST: COPPER ALLOY
- HOLD DOWN FEATURES LOCATED AS SHOWN FOR 8 THRU 14 & 60 THRU 100 POSN ASSEMBLIES (SEE TABLE)
- HOLD DOWN FEATURES LOCATED AS SHOWN FOR 16 THRU 100 POSN ASSEMBLIES (SEE TABLE)
- FINISH: 0.03µm MIN GOLD ON GOLD PLATED AREA, 3.81µm MATTE TIN LEAD ON TIN PLATED AREA. UNDER PLATING SHOULD BE 1.27µm NICKEL ON ENTIRE CONTACT.
- FINISH: 0.03µm MIN GOLD ON GOLD PLATED AREA, 3.81µm MATTE TIN ON TIN PLATE AREA. UNDER PLATING SHOULD BE 1.27µm NICKEL ON ENTIRE CONTACT.
- NOTE DELETED.
- NOTE DELETED.

C



B



12	2.54	-	-	5.08	4	9.65	10	8-104477-2
	1.27	-	12.7	15.24	12	19.81	26	8-104477-1
	1.27	5.72	11.43	13.97	11	18.54	24	8-104477-0
	1.27	17.15	34.29	36.83	29	41.40	60	7-104477-9
	3.18	-	-	6.35	5	10.92	12	7-104477-8
	1.27	29.85	59.69	62.23	49	66.80	100	7-104477-7
	1.27	23.5	46.99	49.53	39	54.10	80	7-104477-6
	1.27	-	27.94	30.48	24	35.05	50	7-104477-5
	1.27	-	21.59	24.13	19	28.70	40	7-104477-4
	1.27	-	15.24	17.78	14	22.35	30	7-104477-3
	1.27	-	8.89	11.43	9	16.00	20	7-104477-2
	1.27	20.96	41.91	44.45	35	49.02	72	7-104477-1
7	2.54	-	-	5.08	4	9.65	10	6-104477-2
	1.27	-	12.7	15.24	12	19.81	26	6-104477-1
	1.27	5.72	11.43	13.97	11	18.54	24	6-104477-0
	1.27	17.15	34.29	36.83	29	41.40	60	5-104477-9
	3.18	-	-	6.35	5	10.92	12	5-104477-8
	1.27	29.85	59.69	62.23	49	66.80	100	5-104477-7
	1.27	23.5	46.99	49.53	39	54.10	80	5-104477-6
	1.27	-	27.94	30.48	24	35.05	50	5-104477-5
	1.27	-	21.59	24.13	19	28.70	40	5-104477-4
	1.27	-	15.24	17.78	14	22.35	30	5-104477-3
	1.27	-	8.89	11.43	9	16.00	20	5-104477-2
	1.27	20.96	41.91	44.45	35	49.02	72	5-104477-1

7

FINISH

DIM_F

DIM_E

DIM_D

DIM_C

B SPACES

DIM_A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SHRISHAIL CHK J. OLSON APVD J. OLSON	20NOV2017 20NOV2017 20NOV2017
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.3 2 PLC ±0.13 3 PLC ±.1 4 PLC ±.1 ANGLES ±0.5°	
MATERIAL		SEE TABLE	
CUSTOMER DRAWING		SCALE 6:1	

TE Connectivity		TE Connectivity	
NAME		HEADER ASSEMBLY, RIGHT ANGLE, DOUBLE ROW, W/SIDE & END LATCHES, AMPMODU System 50	
SIZE		CAGE CODE	
DRAWING NO		RESTRICTED TO	
A100779		C=104477	
SHEET 1		OF 1	
REV AA2			