



THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.

REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN
B		NEW DRAWING	17AUG2022	DS
C		LABEL RELOCATED, PARTS CHANGED	13APR2023	DS
				PM


2406969-1
WITHOUT CABLES
CABLE OUTLET - LEFT




2406969-2
WITHOUT CABLES
CABLE OUTLET - RIGHT





2406969-3
WITHOUT CABLES
CABLE OUTLET - LEFT




2406969-4
WITHOUT CABLES
CABLE OUTLET - RIGHT



AS SHOWN
2406969-1
WITHOUT CABLES



2406969-5
WITHOUT CABLES
CABLE OUTLET - STRAIGHT



NOTES

- STRIPPED ONLY OUTER JACKET, BRAID AND FILLER (IF PRESENT). ELECTRICAL TESTING IS ACCORDING TO APPLICATION SPECIFICATION.
- APPLICATION SPECIFICATION: 114-94648
- APPLICATION SPECIFICATION: 114-94649
- APPLICATION SPECIFICATION: 114-94762
- CUTTING LENGTHS TO BE FIXED BY MANUFACTURING.
- MANUFACTURING CODE:
TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY).
TO BE PRINTED ON LABEL (ITEM 22).
LABEL TO BE APPLIED TO THE CABLE AFTER SUCCESSFUL ELECTRICAL TEST.
- FLAP ASSY (ITEM 36) WILL BE NOT MOUNTED AS SHOWN. BUT PROVIDED AS AN ADDITIONAL COMPONENTS OR ACCESSORIES.

1	9-2337030-1	A	FLAP ASSY.INLET COMBO RIGHT	36
1	8-2337030-1	A	FLAP ASSY.INLET COMBO LEFT	
QTY	ORDER PN	REV	ADDITIONAL COMPONENTS/ ACCESSORIES DESCRIPTION	ITEM NO

4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	ACTUATOR CABLE	35
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	ACTUATOR CABLE	34
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	ACTUATOR CABLE	33
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	ACTUATOR CABLE	32
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	31
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	30
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	29
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	28
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	27
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	26
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	SIGNAL CABLE	25
1	1	1	1	1	1	1	1	1	1	10POS.MICRO MNL.RCPT HSG	24
7	7	7	7	7	7	7	7	7	7	TERMINAL MICRO MATE N LOCK	23
1	1	1	1	1	1	1	1	1	1	LABEL.HELL.TYP 323	22
1	1	1	1	1	1	1	1	1	1	CAB TIE. CLIP. HELL. T18R-HR-N46	21
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	PE CABLE 25mm ²	20
8m	4m	8m	4m	8m	4m	8m	4m	8m	4m	50 mm ² DC CABLE	19
4m	2m	4m	2m	4m	2m	4m	2m	4m	2m	2x6 mm ² AC CABLE	18
4	4	4	4	4	4	4	4	4	4	MQSO.63 Sn rec LL EDS 0.5-0.75	17
4	4	4	4	4	4	4	4	4	4	MQS SGL WIRE SEAL	16
1	1	1	1	1	1	1	1	1	1	4POS MQS REC COD A	15
-	-	-	-	-	-	-	-	-	-	MQS CAVITY PLUG	14
1	1	-	-	-	-	-	-	-	-	COVER, CABLE SEAL, DC	13
-	-	1	1	1	1	-	-	-	-	COVER, CABLE SEAL, DC	12
-	-	-	-	-	-	1	1	1	1	COVER, CABLE SEAL, DC	11
1	1	1	1	1	1	-	-	-	-	FAMILY SEAL, COMBO DC	10
-	-	-	-	-	-	1	1	1	1	FAMILY SEAL, COMBO DC	9
1	1	-	-	-	-	-	-	-	-	COVER, CABLE SEAL, AC	8
-	-	1	1	1	1	1	1	1	1	COVER, CABLE SEAL, AC	7
1	1	1	1	1	1	1	1	1	1	STRAIN RELIEF, AC	6
1	1	1	1	1	1	1	1	1	1	AC FAMILY SEAL	5
1	1	-	-	-	-	-	-	-	-	CABLE EXIT, RECT, COMBO	4
-	-	1	1	-	-	-	-	-	-	CABLE EXIT, RECT, COMBO RIGHT	3
-	-	-	-	1	1	-	-	-	-	CABLE EXIT, RECT, COMBO LEFT	2
-	-	-	-	-	-	-	-	1	1	CABLE EXIT, RECT, COMBO RIGHT	1
1	1	1	1	1	1	-	-	-	-	CABLE EXIT, RECT, COMBO LEFT	0
2	2	2	2	2	2	-	-	-	-	RADIAL SEAL	7
-	-	-	-	-	-	2	2	2	2	PIN, DIA8.0 CONTACT ASSY TYP1 50mm ²	6
2	2	2	2	2	2	-	-	-	-	PIN DIA 8.0 TERMINAL 90 DEG	5
2	2	2	2	2	2	2	2	2	2	SEALING	4
1	1	1	1	1	1	1	1	1	1	PROTECTION CAP.WATER DRAIN	3
1	1	1	1	1	1	1	1	1	1	PIN CONTACT, DIA2.8, PE 25mm ²	2
2	2	2	2	2	2	2	2	2	2	PIN CONTACT, DIA3.6, L/N, ASSY 6mm ²	1
1	1	1	1	1	1	-	-	-	-	INLET HSG, COMBOT, ASSY	0
-	-	-	-	-	-	-	-	1	1	INLET HSG, ADAPTER, COMBOT, ASSY	0
1-5	-5	1-4	-4	1-3	-3	1-2	-2	1-1	-1	DESCRIPTION	ITEM NO

WIRING SCHEDULE:

CAVITY-NO.	IDENTIFICATION	WIRE COLOUR	WIRE CROSS-SECTION
1	L1	RED	6mm ²
2	L2/N	BLACK	6mm ²
3	GROUND/EARTH	BLACK	25mm ²
8	DC+	ORANGE	50mm ²
9	DC-	ORANGE	50mm ²

LENGTH SCHEDULE:

TE PART NO	REV	LENGTH L (mm)	TOLERANCE	CABLE OUTLET
2406969-1	C	2000	+30	LEFT
1-2406969-1	C	4000	+50	LEFT
2406969-2	C	2000	+30	RIGHT
1-2406969-2	C	4000	+50	RIGHT
2406969-3	C	2000	+30	LEFT
1-2406969-3	C	4000	+50	LEFT
2406969-4	C	2000	+30	RIGHT
1-2406969-4	C	4000	+50	RIGHT
2406969-5	C	2000	+30	STRAIGHT
1-2406969-5	C	4000	+50	STRAIGHT

WIRING SCHEDULE FOR SIGNAL CABLE:

PIN NO.	IDENTIFICATION	WIRE COLOR	WIRE SECTION
1	T DC+	OR	0.5mm ²
2	T DC GROUND	GY	0.5mm ²
3	T DC-	RD	0.5mm ²
4	-	-	-
5	-	-	-
6	PROXI OUT	BU	0.5mm ²
7	-	-	-
8	T AC GROUND	BK	0.5mm ²
9	T AC	WH/BU	0.5mm ²
10	CP OUT	VT	0.5mm ²

WIRING SCHEDULE FOR ACTUATOR CABLE:

PIN NO.	WIRE COLOR	WIRE SECTION
1	BN	0.5mm ²
2	BN/BU	0.5mm ²
3	BK/BU	0.5mm ²
4	GN	0.5mm ²

LABEL LEGEND:

STE	TE PART NO., CURRENT REVISION
TE PN: X-#####-Y Rev. ...	PRODUCTION DATE
DD/MM/YY	ELECTRICAL TEST PASSED

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).				DATE: 17AUG2022	FORM: Form 001	NAME: CHARGING INLET CCS1, CABLE ASSY
DRAWN: J. Vais	CHECKED: J. Vais	APPROVED: J. Vais	DATE: 17AUG2022	DATE: 17AUG2022	DATE: 17AUG2022	NAME: CHARGING INLET CCS1, CABLE ASSY
DIMENSIONS: (mm)	0 PLC -	1 PLC -	2 PLC -	3 PLC -	4 PLC -	5 PLC -
MATERIAL: -	FINISH: -	WEIGHT: -	SCALE: 1:1	SHEET: 1	OF: 1	REV: C
CUSTOMER DRAWING				RESTRICTED TO		