


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J4	REVISED PER ECR-25-255998	12SEP2025	SA	DSC

- 1
- WIRE INSULATION DIA = 2.92 [.115] – 4.32 [.170]
- 2
- TONGUE MATERIAL THK = 0.79±0.05 [.031±.002]
- 3
- 0.00254 [.000100] MIN THK. TIN PLATE (ASTM-B545)
- 4
- MATERIAL:
INSULATION: NYLON – BLUE
BODY & SLEEVE: COPPER (ASTM-B152)
- 5
- APPLIES FROM THE METAL EDGE OF BARREL TO
THE CENTERLINE OF STUD



100	LOOSE PC, BOX	8-35559-1
1 KIT = 250 PIECES	LOOSE PIECE	6-35559-0
5000	ON TAPE, REEL	2-35559-1
-	LOOSE PIECE	35559
QTY	DESCRIPTION	PART NO

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221° F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 03JUN09		TE Connectivity												
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300V MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.20[.008] 4 PLC ± - ANGLES ± 0° 30'													
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED				APVD TOM MICHIELUTTI 03JUN09		NAME TERMINAL PIDG, SPADE WIRE SIZE: 16-14 AWG											
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 		FINISH BODY 													
								PRODUCT SPEC —		SIZE A3			CAGE CODE 00779			DRAWING NO C-35559			RESTRICTED TO —		
								APPLICATION SPEC —													
								WEIGHT —													
CUSTOMER DRAWING										SCALE 5:1		SHEET 1 OF 1		REV J4							