






- 1
- CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF 2.54
-
- TOLERANCE NON-CUMULATIVE

2


3

4

LONGEST POSITION SHOWN




SECTION X - X



SECTION W - W

ISOMETRIC VIEW



SCALE 2:1

SCALE 2:1

	10.16	22.86	3	8	2-86264-6
	12.70	25.40	4	10	2-86264-5
△	15.24	27.94	5	12	2-86264-4
△	17.78	30.48	6	14	2-86264-3
	20.32	33.02	7	16	2-86264-2
△	22.86	35.56	8	18	2-86264-1
△	25.40	38.10	9	20	2-86264-0
△	27.94	40.64	10	22	1-86264-9
△	30.48	43.18	11	24	1-86264-8
△	33.02	45.72	12	26	1-86264-7
△	35.56	48.26	13	28	1-86264-6
△	38.10	50.80	14	30	1-86264-5
△	40.64	53.34	15	32	1-86264-4
△	43.18	55.88	16	34	1-86264-3
△	45.72	58.42	17	36	1-86264-2
△	48.26	60.96	18	38	1-86264-1
	50.80	63.50	19	40	1-86264-0
△	53.34	66.04	20	42	86264-9
△	55.88	68.58	21	44	86264-8
△	58.42	71.12	22	46	86264-7
△	60.96	73.66	23	48	86264-6
△	63.50	76.20	24	50	86264-5
△	66.04	78.74	25	52	86264-4
OBSOLETE	68.58	81.28	26	54	86264-3
OBSOLETE	71.12	83.82	27	56	86264-2
	"K" DIM	"L" DIM	NUMBER OF SPACES	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BOB BOLES BQ 31AUG89	TE Connectivity		
DIMENSIONS:		CHK J. GESEFORD 14SEP89			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. GESEFORD 14SEP89	NAME MOD IV CRIMP SNAP-IN CONNECTOR, DOUBLE ROW, 2.54 CENTERS		
	0 PLC ±"	PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
	1 PLC ±0.5	108-25020			
	2 PLC ±0.13	APPLICATION SPEC	A 00779 86264		
	4 PLC ±"	114-25003, 114-25016			
MATERIAL	FINISH	WEIGHT	CUSTOMER DRAWING		
3	-	-	SCALE 4:1 SHEET 1 OF 1 REV P3		